








- 1 MATERIALS AND FINISH
HOUSING: PA 6-6, UL 94-V0, COLOR GREEN.
CLAMP: BRASS, NICKEL PLATED.
DOUBLE SIDE CONTACT SPRING : PHOSPHOR BRONZE, TIN PLATED.
CLAMPING SCREW: M3, BRASS, NICKEL PLATED.
- 2 WIRE SIZE RANGE:
12 - 30 AWG
- 3 NOT CUMULATIVE TOLERANCE.
- 4 PRELIMINARY
- 5 SPECIAL MARKING TO BE PERMANENT BLACK LETTERING
- 6 SPECIAL MARKING TO BE IN PERMANENT BLACK INK
- 7 SPECIAL MARKING TO BE PERMANENT WHITE INK (SEE BACKGROUND)



	DETAIL D	20.32	4	2-284041-9
	DETAIL C	20.32	4	2-284041-8
	DETAIL B	20.32	4	2-284041-7
	DETAIL A	20.32	4	2-284041-6
		127.00	25	2-284041-5
		121.92	24	2-284041-4
		116.84	23	2-284041-3
		111.76	22	2-284041-2
		106.68	21	2-284041-1
		101.60	20	2-284041-0
		96.52	19	1-284041-9
		91.44	18	1-284041-8
		86.36	17	1-284041-7
		81.28	16	1-284041-6
		76.20	15	1-284041-5
		71.12	14	1-284041-4
		66.04	13	1-284041-3
		60.96	12	1-284041-2
		55.88	11	1-284041-1
		50.80	10	1-284041-0
		45.72	9	284041-9
		40.64	8	284041-8
		35.56	7	284041-7
		30.48	6	284041-6
		25.40	5	284041-5
		20.32	4	284041-4
	15.24	3	284041-3	
	10.16	2	284041-2	
	DIM. A	NO OF POS.	PART NUMBER	

1471-9 (3/11)