




Ring Terminal, Non-Insulated

- Ring tongue design assures a secure connection in high vibration applications
- Internal barrel serrations assure good wire contact and maximum tensile strength
- Brazed seam protects terminal barrel from splitting during the crimp process

- Barrel of terminal internally beveled to provide quick and easy wire insertion
- Maximum recommended operating temperature 302°F (150°C)
- UL and CSA rated up to 2000 V per UL 486A/B, where applicable



Part Number	Wire Range		Stud Size		Length		Width		Clearance		Panduit Crimping Tool	Std. Pkg. Qty.	Std. Ctn. Qty.
	AWG	mm ²	In.	mm	In.	mm	In.	mm	In.	mm			
P14-8R-C	18 – 14 AWG	1.0 – 2.5	#8	M4	0.71	18.0	0.31	7.9	0.25	6.4	CT-100A†, CT-200†, CT-600-A†, CT-1570†, CT-2500†	100	1000
P14-10R-C			#10	M5	0.71	18.0	0.31	7.9	0.25	6.4		100	1000
P14-14R-C			1/4"	M6	0.91	23.1	0.46	11.7	0.38	9.7		100	1000
P14-56R-C			5/16"	M8	0.91	23.1	0.46	11.7	0.38	9.7		100	1000
P14-38R-C			3/8"	M10	1.0	25.4	0.53	13.5	0.43	10.9		100	1000
P14-12R-L	14 – 10 AWG	2.5 – 6.0	1/2"	M12	1.20	30.5	0.72	18.3	0.53	13.5	CT-100A†, CT-200†, CT-600-A†, CT-1570†, CT-1701†, CT-2500†	50	500
P10-8R-L			#8	M4	0.78	19.8	0.31	7.9	0.31	7.9		50	500
P10-10R-L			#10	M5	0.81	20.6	0.38	9.7	0.31	7.9		50	500
P10-14R-L			1/4"	M6	0.96	24.4	0.52	13.2	0.38	9.7		50	500
P10-56R-L			5/16"	M8	0.96	24.4	0.52	13.2	0.38	9.7		50	500
P10-38R-L	8 AWG	10.0	3/8"	M10	1.05	26.7	0.58	14.7	0.44	11.2	CT-1701†, CT-2600 with Die Insert CD-2600-8†	50	500
P10-12R-L			1/2"	M12	1.20	30.5	0.72	18.3	0.53	13.5		50	500
P8-10R-Q			#10	M5	1.14	29.0	0.47	11.9	0.43	10.9		25	250
P8-14R-Q			1/4"	M6	1.14	29.0	0.47	11.9	0.43	10.9		25	250
P8-56R-Q			5/16"	M8	1.25	31.8	0.59	15.0	0.51	13.0		25	250
P8-38R-Q	6 AWG	16.0	3/8"	M10	1.25	31.8	0.59	15.0	0.51	13.0	CT-1701†, CT-2600 with Die Insert CD-2600-6†	25	250
P8-12R-Q			1/2"	M12	1.36	34.5	0.82	20.8	0.54	13.7		25	250
P6-10R-E			#10	M5	1.21	30.7	0.47	11.9	0.43	10.9		20	200
P6-14R-E			1/4"	M6	1.21	30.7	0.47	11.9	0.43	10.9		20	200
P6-56R-E			5/16"	M8	1.33	33.8	0.62	15.7	0.51	13.0		20	200
P6-38R-E	4 AWG	25.0	3/8"	M10	1.33	33.8	0.62	15.7	0.51	13.0	CT-1701†, CT-2600 with Die Insert CD-2600-4†	20	200
P6-12R-E			1/2"	M12	1.43	36.3	0.82	20.8	0.51	13.0		20	200
P4-14R-E			1/4"	M6	1.40	35.6	0.55	14.0	0.50	12.7		20	200
P4-56R-E			5/16"	M8	1.46	37.1	0.68	17.3	0.50	12.7		20	200
P4-38R-E			3/8"	M10	1.46	37.1	0.68	17.3	0.50	12.7		20	200
P4-12R-E	2 AWG	35.0	1/2"	M12	1.55	39.4	0.86	21.8	0.53	13.5	CT-1701†, CT-2600 with Die Insert CD-2600-4†	20	200
P2-14R-X			1/4"	M6	1.46	37.1	0.68	17.3	0.58	14.7		10	100
P2-56R-X			5/16"	M8	1.46	37.1	0.68	17.3	0.58	14.7		10	100
P2-38R-X			3/8"	M10	1.46	37.1	0.68	17.3	0.58	14.7		10	100
P2-12R-X			1/2"	M12	1.55	39.4	0.86	21.8	0.58	14.7		10	100

†UL and CSA approved tooling/product combinations.
 For crimping tool information, see page M.46 of SA-NCCB51.
 For the full selection of Panduit Crimping Tools see www.panduit.com.