


## Dimensions: mm (In.)

**Electrical Specifications:**

- Rating: 0.4 Volt-Amps (VA) max. @20V max. (AC or DC)
- Contact Resistance: 20m $\Omega$  max. initial @ 2-4VDC 100mA
- Insulation Resistance: 1,000M $\Omega$  min.
- Dielectric Strength: 1,000 V RMS@ sea level

**Mechanical Specifications:**

- Mechanical Life: 50,000 make-and-break cycles
- Operating Temperature: -30°C to 85°C

**Materials:**

- Case and Bushing: Glass filled Nylon 6/6, flame retardant, heat stabilized
- Plunger: Thenoplastic Polyester, with internal O-ring seal
- Switch Support: Brass or Steel electrontin plated
- Contact: Gold plated copper alloy

**Note:**

- RoHS Compliant by Exemption

**Sealed Sub-Minature Pushbutton Switch**

107-3015-EVX

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Mountain Switch:

107-3015-EVX