

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [21039-0423](#)
Status: **Active**
Overview: Premo-Flex™ FFC and Etched Polyimide Jumpers
Description: 1.00mm Pitch Premo-Flex™ FFC Jumper, Same Side Contacts (Type A), 26 Circuits, 0.051m Cable Length, 0.27mm Cable Thickness, Tin(Sn) Plating

Documents:

[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)
[Product Specification PS-21039-001 \(PDF\)](#)

General

Product Family Cable
Series [21039](#)
Comments Contacts on the same side, Type A
Crimp Quality Equipment Yes
Overview [Premo-Flex™ FFC and Etched Polyimide Jumpers](#)
Product Name Premo-Flex™ FFC Jumper
UPC 800754792745

Physical

Cable Length 0.051m
Circuits (Loaded) 26
Net Weight 1.330/g
Packaging Type Bag
Pitch - Termination Interface 1.00mm
Temperature Range - Operating -40°C to +80°C
Wire Size AWG N/A
Wire/Cable Type Flat Flex Cable

Electrical

Current - Maximum per Contact 1.3A
Voltage - Maximum 30V

Solder Process Data

Duration at Max. Process Temperature (seconds) 30
Max. Cycles at Max. Process Temperature 1
Process Temperature max. C 250

Material Info

Reference - Drawing Numbers

Product Specification PS-21039-001
Sales Drawing SD-21039-001



image - Reference only

Series

EU RoHS

**ELV and RoHS
Compliant**

REACH SVHC

**Contains SVHC: No
Low-Halogen Status
Not Low-Halogen**

China RoHS



**Need more information on product
environmental compliance?**

Email productcompliance@molex.com
For a multiple part number RoHS Certificate of
Compliance, [click here](#)

Please visit the [Contact Us](#) section for any
non-product compliance questions.

Search Parts in this Series

[21039Series](#)

Use With

Any 1.00mm Pitch Molex FFC/FPC
Connector