



LOC		DIST	REVISIONS				
AA	22	P	LTR	DESCRIPTION	DATE	DMN	APVD
		C	REV PER	ECR-08-032447	23FEB2009	DZ	SY



MATERIAL: HOUSING-PCT POLYESTER, BLACK
IR COMPATIBLE, UL 94V-0.
TERMINALS-.33 [.013] THICK PHOS BRONZE
PLATED WITH 1.27 μ m [.000050] THICK HARD
GOLD IN LOCALIZED AREA AND 3.81 μ m [.000150]
THICK MATTE TIN IN SOLDER AREA OVER 1.27 μ m
.000050 THICK NICKEL UNDERPLATE.
SHIELD-0.254 [.010] THICK COPPER ALLOY
PLATED WITH 1.27 μ m [.000050] MINIMUM NICKEL
AND 2.03 μ m [.000080] MINIMUM HOT TIN DIP ON
PCB GROUND TABS.



JACK CAVITY CONFORMS TO FCC RULES AND
REGULATIONS, PART 68 SUBPART F.



5558188

B

B

C

C

D

D

A

A

SUGGESTED PC BOARD LAYOUT
COMPONENT SIDE
SEE APPLICATION SPECIFICATION

5558188-1
PART NO.

THIS DRAWING IS A CONTROLLED DOCUMENT.									
DIMENSIONS:		TOLERANCES UNLESS OTHERWISE SPECIFIED:		DMN C. YATES/LAMATER OK J.WESTMAN 23MAY2005 23MAY2005					
mm		0 Plc ± - 1 Plc ± - 2 Plc ± 0.254[.01] 3 Plc ± 0.127[.005] ANGLES ± ± -		APVD S.EICKLINGER 23MAY2005					
MATERIAL SEE NOTE 1		FINISH SEE NOTE 1		NAME Tyco Electronics Corporation Harrisburg, Pa 17105-3608					
0 Plc ± - 1 Plc ± - 2 Plc ± 0.254[.01] 3 Plc ± 0.127[.005] ANGLES ± ± -		PRODUCT SPEC 108-1163-1		MODULAR JACK ASSEMBLY, 4 PORT,8 POSITION, RIGHT ANGLE, SHIELDED					
APPLICATION SPEC 114-2048		WEIGHT -		SIZE A2					
CAGE CODE 00779		DRAWING NO 5558188		RESTRICTED TO -					
CUSTOMER DRAWING		SCALE 2:1		SHEET 1		OF 1		REV C	