



LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
J	—		G2	REVISED	ECO-15-008937	15JUN15	KF RK

D



C

B


A




- ① Z 面より2mmの範囲で測定。
2. 適用プリント基板厚：1.6mm
3. 嵌合相手ハウジング型番：174046, 174047
4. 推奨取付けねじ：JIS B1115, B1122 タッピンねじ, なべ2種
呼び径3, 長さ7mm以上 (締付けトルク：0.4N・m以下)
5. 製品規格番号：108-5244, 取扱説明書：411-5883
⑥ 回路番号：FIG.1 参照
- ① TO BE MEASURED WITHIN 2mm FROM Z
2. APPLICABLE P.CBOARD THICKNESS: 1.6mm
3. THE MATING PLUG HOUSING PART NUMBER: 174046, 174047
4. RECOMMENDED MOUNTING SCREW: 3mm DIA, 7mm LENGTH (MIN.)
PAN HEAD, CLASS 2 TAPPING SCREW SPECIFIED IN JIS B1115,
B1122 (TIGHTENING TORQUE: 0.4N・m MAX.)
5. PRODUCT SPECIFICATION: 108-5244
INSTRUCTION SHEET: 411-5883
⑥ CIRCUIT NUMBER: SEE FIG.1



A-A



⑥ FIG.1



OBSOLETE	SELECTIVE-TIN (MATTE)	SELECTIVE GOLD	1~36	BLACK	1-5174146-2
	SELECTIVE-TIN	PRE-TIN	-	BLACK	2-174146-2
	TIN-LEAD	SELECTIVE GOLD	1~36	BLACK	1-174146-2
	PRE-TIN		-	GREEN	174146-4
	PRE-TIN × 35		21	BLACK	174146-3
	TIN-LEAD	SELECTIVE GOLD × 1			
	PRE-TIN		-	BLACK	174146-2
CONTACT FINISH 半田付け部		CONTACT SIDE 接触部側	GOLD PLATED CIRCUIT NO 金めっき回路番号	COLOR 色	PART NUMBER 製品型番
CONTACT FINISH コンタクト仕上					

TOLERANCE UNLESS OTHERWISE SPECIFIED: 一般公差	
0<×≤ 10	: ±0.2
10<×≤ 30	: ±0.25
30<×≤ 100	: ±0.3
ANGLE	: ±3°
角度	

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN T.SHINOHARA 06JAN09	 TE Connectivity					
DIMENSIONS: mm		CHK K.BETSUI 06JAN09						
	TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ± 1 PLC ± 2 PLC ± 3 PLC ± 4 PLC ± ANGLES ± FINISH	APVD K.BETSUI 06JAN09	NAME 040 SERIES MULTI-LOCK I/O CONNECTOR 36POSITION CAP HOUSING ASSEMBLY					
		PRODUCT SPEC SEE NOTE 6						
		APPLICATION SPEC —						
		MATERIAL HOUSING: PBT CONTACT: BRASS	SEE TABLE	WEIGHT 17.5 g	SIZE A2	CAGE CODE 00779	DRAWING NO C=174146	RESTRICTED TO —
		CUSTOMER DRAWING			SCALE 2:1	SHEET 1 of 1	REV G2	