

# SPECIFICATION OF FS SERIES

## APPLICATIONS

The rectangular solid ferrites are used for EMI suppression on flat cable assemblies.

- \* Internal floppy disk ribbon cables.
- \* Internal ribbon cables between circuit and data connectors.
- \* Internal ribbon cables with 8,16,32 or 64 bit digital signal busses.

## ORDERING CODE

K5B FS 45.2 x 6.5 x 12 - 1.3 - G□  
 (1) (2) (3) (4) (5) (6) (7)

- (1) MATERIAL  
 (2) PRODUCT CODE  
 (3) A DIM.  
 (4) B DIM.  
 (5) C DIM.  
 (6) E DIM.  
 (7) DOUBLE SIDED ADHESIVE TAPE



## SHAPE




FIG 1




FIG 2




FIG 3




FIG 4




FIG 5

## DIMENSIONS & CHARACTERISTICS

UNIT:mm

| NO. | ORDERING CODE           | A          | B         | C          | D          | E         | Fig |
|-----|-------------------------|------------|-----------|------------|------------|-----------|-----|
| 1   | FS 5x3x9-1.0            | 5.00±0.20  | 3.00±0.20 | 9.00±0.40  | 3.00±0.20  | 1.00±0.20 | 3   |
| 2   | FS 5.5x3x9-1.4          | 5.50±0.20  | 3.00±0.20 | 9.00±0.30  | 4.00±0.20  | 1.40±0.20 | 3   |
| 3   | FS 6.5x3.8x9-1.4        | 6.50±0.20  | 3.80±0.20 | 9.00±0.30  | 4.00±0.20  | 1.40±0.20 | 3   |
| 4   | FS 7.5x5.3x9-2.8        | 7.50±0.30  | 5.30±0.20 | 9.00±0.30  | 5.00±0.25  | 2.80±0.20 | 3   |
| 5   | FS 7.5x5.3x12-2.8       | 7.50±0.30  | 5.30±0.20 | 12.00±0.50 | 5.00±0.25  | 2.80±0.20 | 3   |
| 6   | FS 9.1x5.6x7.8-3.7      | 9.10±0.20  | 5.60±0.20 | 7.80±0.30  | 7.20±0.20  | 3.70±0.20 | 3   |
| 7   | FS 9.5x3x12-0.8         | 9.50±0.30  | 3.00±0.20 | 12.00±0.50 | 7.60±0.20  | 0.80±0.20 | 3   |
| 8   | FS 10x3.2x3-1.0         | 10.00±0.30 | 3.20±0.20 | 3.00±0.50  | 8.00±0.30  | 1.00±0.20 | 3   |
| 9   | FS 10x3.2x7-1.0         | 10.00±0.30 | 3.20±0.20 | 7.00±0.30  | 8.00±0.30  | 1.00±0.20 | 3   |
| 10  | FS 10x3.2x8-1.0         | 10.00±0.30 | 3.20±0.20 | 8.00±0.40  | 8.00±0.30  | 1.00±0.20 | 3   |
| 11  | FS 13.84x3.94x1.88-1.52 | 13.84±0.15 | 3.94±0.15 | 1.88±0.15  | 9.78±0.15  | 1.52±0.15 | 5   |
| 12  | FS 14.7x2.75x6-0.7      | 14.70±0.40 | 2.75±0.30 | 6.00±0.30  | 11.00±0.40 | 0.70±0.30 | 2   |
| 13  | FS 14.7x2.75x12-0.7     | 14.70±0.40 | 2.75±0.30 | 12.00±0.40 | 11.00±0.40 | 0.70±0.30 | 2   |

※Other sizes are available upon request.
















※All the data listed in this catalogue are for reference only, King Core reserves the right to alter or revise the specifications without prior notification.



KING CORE ELECTRONICS INC.  
 Tel:886-3-4698855 Fax:886-3-4691395

No.269,Nanfong Rd.,Pingjhen City,Taoyuan County,Taiwan  
 E-mail:kc@mail.kingcore.com.tw Web Site:http://www.kingcore.com.tw

# SPECIFICATION OF FS SERIES



※Other sizes are available upon request.

※All the data listed in this catalogue are for reference only, King Core reserves the right to alter or revise the specifications without prior notification.







**KING CORE ELECTRONICS INC.**  
Tel:886-3-4698855 Fax:886-3-4691395

No.269,Nanfong Rd.,Pingjhen City,Taoyuan County,Taiwan  
E-mail:kc@mail.kingcore.com.tw Web Site:http://www.kingcore.com.tw

# SPECIFICATION OF FS SERIES

| NO. | ORDERING CODE        | A          | B                 | C          | D          | E                 | Fig |
|-----|----------------------|------------|-------------------|------------|------------|-------------------|-----|
| 14  | FS 16x3x5-0.8        | 16.00±0.40 | 3.00±0.20         | 5.00±0.30  | 11.50±0.40 | 0.50(+0.60/-0.00) | 2   |
| 15  | FS 16x3x8-0.8        | 16.00±0.40 | 3.00±0.20         | 8.00±0.40  | 11.50±0.40 | 0.50(+0.60/-0.00) | 2   |
| 16  | FS 16x4x4-0.8        | 16.00±0.40 | 4.00±0.20         | 4.00±0.30  | 11.50±0.40 | 0.50(+0.60/-0.00) | 2   |
| 17  | FS 16x5x3-0.8        | 16.00±0.60 | 5.00(+0.00/-0.70) | 3.00±0.30  | 11.50±0.50 | 0.50(+0.60/-0.00) | 2   |
| 18  | FS 16x5x6-0.8        | 16.00±0.40 | 5.00(+0.00/-0.70) | 6.00±0.50  | 11.50±0.40 | 0.50(+0.60/-0.00) | 2   |
| 19  | FS 16x5x8-0.8        | 16.00±0.40 | 5.00(+0.00/-0.70) | 8.00±0.40  | 11.50±0.40 | 0.50(+0.60/-0.00) | 2   |
| 20  | FS 16x5x12-0.8       | 16.00±0.40 | 5.00(+0.00/-0.70) | 12.00±0.50 | 11.50±0.40 | 0.50(+0.60/-0.00) | 2   |
| 21  | FS 16x5x12-1.2       | 16.00±0.40 | 5.00(+0.00/-0.70) | 12.00±0.50 | 11.50±0.40 | 1.20±0.30         | 2   |
| 22  | FS 16x5x15-0.8       | 16.00±0.40 | 5.00(+0.00/-0.70) | 15.00±0.50 | 11.50±0.40 | 0.50(+0.60/-0.00) | 2   |
| 23  | FS 16x5x20-0.8       | 16.00±0.40 | 5.00(+0.00/-0.70) | 20.00±0.50 | 11.50±0.40 | 0.50(+0.60/-0.00) | 2   |
| 24  | FS 18x5x8-1.0        | 18.00±1.00 | 5.00±0.30         | 8.00±0.50  | 14.00±0.50 | 1.00±0.50         | 2   |
| 25  | FS 18x5x12-1.0       | 18.00±1.00 | 5.00±0.30         | 12.00±0.50 | 14.00±0.50 | 1.00±0.50         | 2   |
| 26  | FS 18.3x12x30-5.25   | 18.30±0.40 | 12.00±0.40        | 30.00±0.50 | 11.50±0.40 | 5.25±0.25         | 2   |
| 27  | FS 18.9x6.5x20-1.8   | 18.90±0.50 | 6.50±0.40         | 20.00±0.50 | 14.00±0.60 | 1.80±0.30         | 2   |
| 28  | FS 19x3x8-0.8        | 19.00±0.40 | 3.00±0.20         | 8.00±0.40  | 14.50±0.40 | 0.50(+0.60/-0.00) | 2   |
| 29  | FS 19x6.5x12-1.8     | 19.00±0.70 | 6.50±0.50         | 12.00±0.50 | 14.00±0.40 | 1.80±0.20         | 2   |
| 30  | FS 20.5x3.5x15-0.8   | 20.50±0.60 | 3.50±0.15         | 15.00±0.40 | 16.50±0.40 | 0.80±0.15         | 2   |
| 31  | FS 23.3x2.5x7-0.9    | 23.30±0.70 | 2.50±0.20         | 7.00±0.30  | 20.00±0.50 | 0.90±0.20         | 1   |
| 32  | FS 23.3x3x6-0.9      | 23.30±0.70 | 3.00±0.40         | 6.00±0.50  | 20.00±0.50 | 0.90±0.20         | 1   |
| 33  | FS 23.3x3x7-0.9      | 23.30±0.70 | 3.00(+0.40/-0.20) | 7.00±0.30  | 20.00±0.50 | 0.90±0.20         | 1   |
| 34  | FS 23.3x3x10-0.9     | 23.30±0.70 | 3.00(+0.40/-0.20) | 10.00±0.40 | 20.00±0.50 | 0.90±0.20         | 1   |
| 35  | FS 23.3x3x12-0.9     | 23.30±0.70 | 3.00(+0.40/-0.20) | 12.00±0.50 | 20.00±0.50 | 0.90±0.20         | 1   |
| 36  | FS 23.3x3x15-0.9     | 23.30±0.70 | 3.00(+0.40/-0.20) | 15.00±0.60 | 20.00±0.50 | 0.90±0.20         | 1   |
| 37  | FS 23.8x3.2x15-1.1   | 23.80±0.80 | 3.20±0.20         | 15.00±0.60 | 18.70±0.80 | 1.10±0.40         | 1   |
| 38  | FS 23.8x6.3x7-1.1    | 23.80±0.80 | 6.30±0.40         | 7.00±0.30  | 18.70±0.80 | 1.10±0.40         | 2   |
| 39  | FS 23.8x6.3x12.5-1.1 | 23.80±0.80 | 6.30±0.40         | 12.50±0.40 | 18.70±0.80 | 1.10±0.40         | 2   |
| 40  | FS 24x12x30-4.0      | 24.00±0.70 | 12.00±0.40        | 30.00±0.70 | 15.00±0.50 | 4.00±0.40         | 2   |
| 41  | FS 24.5x5x12-0.5     | 24.50±0.70 | 5.00(+0.00/-0.70) | 12.00±0.40 | 20.00±0.50 | 0.50(+0.60/-0.00) | 2   |
| 42  | FS 24.5x5x20-0.5     | 24.50±0.50 | 5.00(+0.00/-0.70) | 20.00±0.60 | 20.00±0.50 | 0.50(+0.60/-0.00) | 2   |
| 43  | FS 25x3.7x20-0.7     | 25.00±0.70 | 3.70±0.40         | 20.00±0.60 | 22.00±0.50 | 0.70(+0.50/-0.10) | 2   |
| 44  | FS 25.5x3x9-0.65     | 25.50±0.70 | 3.00±0.20         | 9.00±0.40  | 21.50±0.50 | 0.65±0.30         | 2   |
| 45  | FS 25.5x3x12-0.65    | 25.50±0.70 | 3.00±0.20         | 12.00±0.50 | 21.50±0.50 | 0.65±0.30         | 2   |
| 46  | FS 25.5x3x9-0.65     | 25.50±0.70 | 3.00±0.20         | 9.00±0.40  | 21.50±0.50 | 0.65±0.30         | 2   |
| 47  | FS 25.5x5x15-0.65    | 25.50±0.70 | 5.00±0.30         | 15.00±0.60 | 21.50±0.50 | 0.65±0.30         | 1   |



※Other sizes are available upon request.


※All the data listed in this catalogue are for reference only, King Core reserves the right to alter or revise the specifications without prior notification.



**KING CORE ELECTRONICS INC.**  
Tel:886-3-4698855 Fax:886-3-4691395

No.269,Nanfong Rd.,Pingjhen City,Taoyuan County,Taiwan  
E-mail:kc@mail.kingcore.com.tw Web Site:http://www.kingcore.com.tw

# SPECIFICATION OF FS SERIES



※Other sizes are available upon request.


※All the data listed in this catalogue are for reference only, King Core reserves the right to alter or revise the specifications without prior notification.



**KING CORE ELECTRONICS INC.**  
Tel:886-3-4698855 Fax:886-3-4691395

No.269,Nanfong Rd.,Pingjhen City,Taoyuan County,Taiwan  
E-mail:kc@mail.kingcore.com.tw Web Site: <http://www.kingcore.com.tw>

# SPECIFICATION OF FS SERIES



※Other sizes are available upon request.

※All the data listed in this catalogue are for reference only, King Core reserves the right to alter or revise the specifications without prior notification.















**KING CORE ELECTRONICS INC.**  
Tel:886-3-4698855 Fax:886-3-4691395

No.269,Nanfong Rd.,Pingjhen City,Taoyuan County,Taiwan  
E-mail:kc@mail.kingcore.com.tw Web Site: <http://www.kingcore.com.tw>

# SPECIFICATION OF FS SERIES

| NO. | ORDERING CODE        | A          | B          | C          | D                  | E                 | Fig |
|-----|----------------------|------------|------------|------------|--------------------|-------------------|-----|
| 48  | FS 28.5x6.5x8-0.8    | 28.50±1.00 | 6.50±0.50  | 8.00±0.40  | 23.50±0.50         | 0.80±0.30         | 2   |
| 49  | FS 28.5x6.5x15-1.0   | 28.50±1.00 | 6.50±0.50  | 15.00±0.60 | 23.50±0.70         | 1.00±0.20         | 2   |
| 50  | FS 28.5x6.5x18-1.0   | 28.50±1.00 | 6.50±0.50  | 18.00±0.70 | 23.50±0.70         | 1.00±0.20         | 2   |
| 51  | FS 28.6x7.7x10-1.7   | 28.60±0.50 | 7.70±0.50  | 10.00±0.40 | 23.50±0.50         | 1.70±0.50         | 2   |
| 52  | FS 28.6x7.7x14.6-1.7 | 28.60±0.50 | 7.70±0.50  | 14.60±0.60 | 23.50±0.50         | 1.70±0.50         | 2   |
| 53  | FS 31x3x8-1.0        | 31.00±1.00 | 3.00±0.20  | 8.00±0.40  | 27.00±0.70         | 1.00±0.20         | 2   |
| 54  | FS 31x3x12-1.0       | 31.00±1.00 | 3.00±0.20  | 12.00±0.50 | 27.00±0.70         | 1.00±0.20         | 2   |
| 55  | FS 31x4x20-0.7       | 31.00±1.00 | 4.00±0.30  | 20.00±0.60 | 27.00±0.70         | 0.70±0.20         | 2   |
| 56  | FS 31x5x9-1.0        | 31.00±1.00 | 5.00±0.30  | 9.00±0.40  | 27.00±0.70         | 1.00±0.20         | 2   |
| 57  | FS 31x5x12-1.0       | 31.00±1.00 | 5.00±0.30  | 12.00±0.50 | 27.00±0.70         | 1.00±0.20         | 2   |
| 58  | FS 31x5x18-1.0       | 31.00±1.00 | 5.00±0.30  | 18.00±0.60 | 27.00±0.70         | 1.00±0.20         | 2   |
| 59  | FS 32x4x25-0.7       | 32.00±1.00 | 4.00±0.20  | 25.00±0.50 | 27.00(+2.00/-0.00) | 0.70(+0.30/-0.00) | 2   |
| 60  | FS 32x6x25-0.85      | 32.00±1.00 | 6.00±0.30  | 25.00±1.00 | 28.00±0.70         | 0.85±0.20         | 2   |
| 61  | F3S 32x11.8x16-1.0   | 32.00±0.80 | 11.80±0.50 | 16.00±0.60 | 27.00±0.90         | 1.00±0.30         | 4   |
| 62  | FS 33.5x6.5x8-1.3    | 33.50±1.00 | 6.50±0.50  | 8.00±0.30  | 27.00±0.70         | 1.30(+0.50/-0.30) | 2   |
| 63  | FS 33.5x6.5x10-1.3   | 33.50±1.00 | 6.50±0.50  | 10.00±0.40 | 27.00±0.70         | 1.30(+0.50/-0.30) | 2   |
| 64  | FS 33.5x6.5x12-1.3   | 33.50±1.00 | 6.50±0.50  | 12.00±0.50 | 27.00±0.70         | 1.30(+0.50/-0.30) | 2   |
| 65  | FS 33.5x6.5x15-1.3   | 33.50±1.00 | 6.50±0.50  | 15.00±0.50 | 27.00±0.70         | 1.30(+0.50/-0.30) | 2   |
| 66  | FS 33.5x6.5x20-1.3   | 33.50±1.00 | 6.50±0.50  | 20.00±0.60 | 27.00±0.70         | 1.30(+0.50/-0.30) | 2   |



※Other sizes are available upon request.

※All the data listed in this catalogue are for reference only. King Core reserves the right to alter or revise the specifications without prior notification.




**KING CORE ELECTRONICS INC.**  
Tel:886-3-4698855 Fax:886-3-4691395

No.269,Nanfong Rd.,Pingjhen City,Taoyuan County,Taiwan  
E-mail:kc@mail.kingcore.com.tw Web Site:http://www.kingcore.com.tw



# SPECIFICATION OF FS SERIES



※Other sizes are available upon request.

※All the data listed in this catalogue are for reference only, King Core reserves the right to alter or revise the specifications without prior notification.



**KING CORE ELECTRONICS INC.**

Tel: 886-3-4698855

Fax: 886-3-4691395













E-mail: [kc@mail.kingcore.com.tw](mailto:kc@mail.kingcore.com.tw)

No. 269, Nanfong Rd., Pingjhen City, Taoyuan County, Taiwan

Web Site: <http://www.kingcore.com.tw>

# SPECIFICATION OF FS SERIES

| NO. | ORDERING CODE           | A          | B          | C          | D          | E                 | Fig |
|-----|-------------------------|------------|------------|------------|------------|-------------------|-----|
| 67  | FS 36x6.5x18-0.6        | 36.00±1.00 | 6.50±0.50  | 18.00±0.60 | 31.00±0.70 | 0.60±0.30         | 2   |
| 68  | FS 36x7.5x8-1.0         | 36.00±1.00 | 7.50±0.50  | 8.00±0.40  | 31.00±0.70 | 1.00±0.20         | 2   |
| 69  | FS 36x7.5x20-1.0        | 36.00±1.00 | 7.50±0.50  | 20.00±1.00 | 31.00±0.70 | 1.00±0.20         | 2   |
| 70  | FS 36x7.5x30-1.0        | 36.00±1.00 | 7.50±0.50  | 30.00±0.80 | 31.00±0.70 | 1.00±0.20         | 2   |
| 71  | FS 36x7.5x36-1.0        | 36.00±1.00 | 7.50±0.50  | 36.00±1.00 | 31.00±0.70 | 1.00±0.20         | 2   |
| 72  | FS 36.6x5x12-0.8        | 36.00±1.00 | 5.00±0.20  | 12.00±0.50 | 32.40±0.70 | 0.80±0.30         | 2   |
| 73  | FS 38.5x4x12-0.8        | 38.50±1.00 | 4.00±0.30  | 12.00±0.50 | 35.00±0.70 | 0.80±0.30         | 2   |
| 74  | FS 38.5x4x15-0.8        | 38.50±1.00 | 4.00±0.50  | 15.00±0.60 | 35.00±0.70 | 0.80±0.30         | 2   |
| 75  | FS 38.53x12.06x25.4-1.9 | 38.53±0.58 | 12.06±0.38 | 25.40±0.76 | 26.77±0.76 | 1.90±0.38         | 1   |
| 76  | FS 40x6.5x6-1.3         | 40.00±1.00 | 6.50±0.50  | 6.00±0.30  | 35.00±0.70 | 1.30(+0.50/-0.30) | 2   |
| 77  | FS 40x6.5x8-1.3         | 40.00±1.00 | 6.50±0.50  | 8.00±0.40  | 35.00±0.70 | 1.30(+0.50/-0.30) | 2   |
| 78  | FS 40x6.5x10-1.3        | 40.00±1.00 | 6.50±0.50  | 10.00±0.40 | 35.00±0.70 | 1.30(+0.50/-0.30) | 2   |
| 79  | FS 40x6.5x12-1.3        | 40.00±1.00 | 6.50±0.50  | 12.00±0.50 | 35.00±0.70 | 1.30(+0.50/-0.30) | 2   |
| 80  | FS 40x6.5x12-2.0        | 40.00±1.00 | 6.50±0.50  | 12.00±0.50 | 35.00±0.70 | 2.00±0.30         | 2   |
| 81  | FS 40x6.5x15-1.3        | 40.00±1.00 | 6.50±0.50  | 15.00±0.60 | 35.00±0.70 | 1.30(+0.50/-0.30) | 2   |
| 82  | FS 40x6.5x18-1.3        | 40.00±1.00 | 6.50±0.50  | 18.00±0.70 | 35.00±0.70 | 1.30(+0.50/-0.30) | 2   |
| 83  | FS 40x6.5x20-1.3        | 40.00±1.00 | 6.50±0.50  | 20.00±0.60 | 35.00±0.70 | 1.30(+0.50/-0.30) | 2   |
| 84  | FS 40x11.4x5-7.4        | 40.00±1.00 | 11.40±0.50 | 5.00±0.40  | 32.00±0.80 | 7.40±0.50         | 3   |
| 85  | FS 45.1x12.5x28.5-1.5   | 45.10±0.76 | 12.50±0.25 | 28.50±0.64 | 34.40±0.64 | 1.50±0.25         | 1   |
| 86  | FS 45.2x6.5x12-1.3      | 45.20±1.00 | 6.50±0.50  | 12.00±0.50 | 40.00±0.80 | 1.30(+0.50/-0.30) | 2   |
| 87  | FS 45.2x6.5x15-1.3      | 45.20±1.00 | 6.50±0.50  | 15.00±0.60 | 40.00±0.80 | 1.30(+0.50/-0.30) | 2   |



※Other sizes are available upon request.

※All the data listed in this catalogue are for reference only, King Core reserves the right to alter or revise the specifications without prior notification.


















**KING CORE ELECTRONICS INC.**  
Tel:886-3-4698855 Fax:886-3-4691395

No.269,Nanfong Rd.,Pingjhen City,Taoyuan County,Taiwan  
E-mail:kc@mail.kingcore.com.tw Web Site:http://www.kingcore.com.tw



# SPECIFICATION OF FS SERIES



※Other sizes are available upon request.

※All the data listed in this catalogue are for reference only, King Core reserves the right to alter or revise the specifications without prior notification.



KING CORE ELECTRONICS INC.

Tel:886-3-4698855

Fax:886-3-4691395


E-mail:kc@mail.kingcore.com.tw

No.269,Nanfong Rd.,Pingjhen City,Taoyuan County,Taiwan

Web Site:http://www.kingcore.com.tw

# SPECIFICATION OF FS SERIES

| NO. | ORDERING CODE      | A          | B          | C          | D                  | E                 | Fig |
|-----|--------------------|------------|------------|------------|--------------------|-------------------|-----|
| 88  | FS 49.6x6.5x8-1.3  | 49.60±1.00 | 6.50±0.50  | 8.00±0.40  | 44.00±0.80         | 1.30(+0.50/-0.30) | 2   |
| 89  | FS 49.6x6.5x10-1.3 | 49.60±1.00 | 6.50±0.50  | 10.00±0.40 | 44.00±0.80         | 1.30(+0.50/-0.30) | 2   |
| 90  | FS 49.6x6.5x12-1.3 | 49.60±1.00 | 6.50±0.50  | 12.00±0.50 | 44.00±0.80         | 1.30(+0.50/-0.30) | 2   |
| 91  | FS 49.6x6.5x15-1.3 | 49.60±1.00 | 6.50±0.50  | 15.00±0.50 | 44.00±0.80         | 1.30(+0.50/-0.30) | 2   |
| 92  | FS 49.6x7x12-1.8   | 49.60±1.00 | 7.00±0.50  | 12.00±0.50 | 44.00±0.80         | 1.80±0.40         | 2   |
| 93  | FS 50x6.5x12-1.4   | 50.00±1.00 | 6.50±0.50  | 12.00±0.50 | 44.90±0.80         | 1.40±0.20         | 2   |
| 94  | FS 57.6x6.5x12-1.3 | 57.60±1.20 | 6.50±0.50  | 12.00±0.50 | 52.00±0.90         | 1.30(+0.50/-0.30) | 2   |
| 95  | FS 58.6x7.5x20-1.3 | 58.60±1.20 | 7.50±0.50  | 20.00±0.60 | 52.00±0.90         | 1.30(+0.50/-0.30) | 2   |
| 96  | FS 60x12x12.7-2.2  | 60.00±1.00 | 12.00±0.50 | 12.70±0.60 | 48.50±0.80         | 2.20±0.40         | 1   |
| 97  | FS 60.6x6.5x12-1.3 | 60.60±1.20 | 6.50±0.50  | 12.00±0.50 | 55.20(+1.00/-0.50) | 1.30(+0.50/-0.30) | 2   |



※Other sizes are available upon request.

※All the data listed in this catalogue are for reference only, King Core reserves the right to alter or revise the specifications without prior notification.



**KING CORE ELECTRONICS INC.**

Tel:886-3-4698855

Fax:886-3-4691395

E-mail:kc@mail.kingcore.com.tw

No.269,Nanfong Rd.,Pingjhen City,Taoyuan County,Taiwan

Web Site:http://www.kingcore.com.tw