


D

C

B

A



1 STAMP AMP 2W* 60-75 APPROX AS SHOWN

321253
AMP
PART NUMBER

AMP INCORPORATED CUSTOMER SERVICE SYSTEMS			THIS DRAWING IS A CONTROLLED DOCUMENT FOR AMP INCORPORATED. IT IS SUBJECT TO CHANGE AND THE CONTROLLING ENGINEERING ORGANIZATION SHOULD BE CONTACTED FOR THE LATEST REVISION.		DWN DK SCHRUM 020CT97		AMP Incorporated Harrisburg, PA 17105-3608			
FOR ADDITIONAL PRODUCT INFORMATION OR COPIES OF DRAWINGS AND TECHNICAL DOCUMENTS	PRODUCT INFORMATION CENTER 1-800-522-6752	RECOMMENDED OPERATING TEMPERATURE: 170°C MAX	DIMENSIONS: mm [INCHES]	TOLERANCES UNLESS OTHERWISE SPECIFIED: 	CHK MJ SPICER 030CT97	AMP				
		VOLTAGE RATING: NOT APPLICABLE				APVD JL MECKLEY 030CT97	NAME TERMINAL, RING TONGUE, FLAG, SOLISTRAND™			
FOR APPLICATION TOOLING INFORMATION	TOOLING ASSISTANCE CENTER 1-800-722-1111	WIRE CROSS SECTIONAL AREA RANGE: 26.7-42.4mm² [52,600-83,700] CIR MILS SOLID OR STRANDED	MATERIAL COPPER PER ASTM B-152 ANNEALED	FINISH TIN PLATE 0.00254[.000100] MIN THK PER ASTM B-545	PRODUCT SPEC -	SIZE A3	CAGE CODE 00779	DRAWING NO C-321253		
FOR ORDER ENTRY	1-800-526-5142				APPLICATION SPEC -	WEIGHT -	CUSTOMER DRAWING			SCALE 2:1