


		REVISIONS					
		REV	DESCRIPTION	DATE	APPROVED		
		02 ₀	REVISED	6/09/94	<i>DCmelB</i>		
NOTES: 1. CAPTURED CENTER CONTACT .XXX = in XX.X = mm		COUPLING NUT		STAINLESS STEEL PER ASTM-A484 AND ASTM-A582, TYPE 303		PASSIVATE PER QQ-P-35	
		DIELECTRIC		TFE FLUOROCARBON PER ASTM-D-1457		N/A	
		CENTER CONTACT HOUSING		BERYLLIUM COPPER PER ASTM-B-196 OR ASTM-B-197, ALLOY C17300, CONDITION H		GOLD PLATE PER MIL-G-45204	
		RETAINING RING		BERYLLIUM COPPER PER ASTM-B-194, ALLOY C17200, CONDITION H		N/A	
		GASKET		SILICONE RUBBER PER ZZ-R-765		N/A	
COMPONENT		MATERIAL		FINISH			
UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN INCHES		DRAWN BY RMF		DATE 6/3/94		 AMP Incorporated 140 Fourth Avenue Waltham, MA 02451-7599	
FRAC. DEC. ANGLES		CHECKED BY BB		DATE 6/10/94			
± 1/64 ±.005 ± 1°		APPD BY TMD		DATE 6/09/94			
These drawings and specifications are the property of M/A COM Interconnect Div. and shall not be reproduced or copied or used in whole or in part as the basis for the manufacture or sale of item(s) without written permission.		USE ASSY PROCEDURE		TITLE OSM PLUG TO OSMP JACK ADAPTER			
		NO. A.P. N/A		SIZE B		CODE IDENT NO. 26805	
		SCALE 8:1		2982-2241-00		REV 02 ₀	
				SHEET 1 OF 1			