

NOTES:

① MAT'L: COPPER (STOCK TKN. $\frac{.050}{1.27}$)
 PLATING: ELECTRO-TIN (.0003 MIN.)

② BRAZED SEAM


STUD SIZES: ($\pm .005$)

02 = .094 76 = .453
 04 = .119 12 = .515
 06 = .146
 08 = .173
 10 = .198
 14 = .265
 56 = .328
 38 = .390

"UL" LISTING #E32244
 "CSA" LISTING #18689

ALL DIMENSIONS = $\frac{\text{INCHES}}{\text{MM}}$

WIRE SIZE: 16-14 AWG
 1.0-2.5 MM²



PART NUMBER	"W" ±.010	"C" MIN.	"L" MAX.				AVAILABLE STUD SIZES	
B-301-	$\frac{.750}{19.05}$	$\frac{.611}{15.52}$	$\frac{1.280}{32.51}$				14HD, 56HD, 38HD, 76HD, 12HD	
B-328-	$\frac{.375}{9.53}$	$\frac{.303}{7.70}$	$\frac{.785}{19.94}$				06HD, 08HD, 10HD	
B-330-	$\frac{.530}{13.46}$	$\frac{.393}{9.98}$	$\frac{.952}{24.18}$				10HD, 14HD, 56HD	
B-336-	$\frac{.282}{7.16}$	$\frac{.306}{7.77}$	$\frac{.741}{18.82}$				04HD, 06HD, 08HD	
B-340-	$\frac{.592}{15.04}$	$\frac{.466}{11.84}$	$\frac{1.056}{26.82}$				10HD, 14HD, 56HD, 38HD	
DIMENSIONAL TOLERANCES UNLESS OTHERWISE SPECIFIED			REFERENCE	SCALE: NTS	DATE	TITLE:		
				DRWN. BY: JJ	11-28-84	RING TONGUE HEAVY DUTY TERMINAL VERSAKRIMP 300-SERIES		
FRAC.	DEC.	ANG.		CHKD. BY: GL	12-13-84		DWG. NO.	A
±	±	±		APPRD. BY:			CUSTOMER DWG.	

FILE NO.

BHD - CD-301 - 01

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Molex:

[19056-0079](#) [19056-0081](#) [19056-0087](#)