

tesa® 51571

Double-sided non-woven tape

PRODUCT INFORMATION

Product Description

tesa® 51571 is a double-sided tape with a non-woven backing. It is used for permanent mounting of metal and plastic materials, e.g. aluminium, polystyrene, polypropylene, ABS. The very thick layer of adhesive bonds extremely well on uneven surfaces and has a very high initial bond.

Main Application

tesa® 51571 is used for applications such as:
Mounting of evaporator plates in the production of refrigerators

Technical Data

■ Backing material	non-woven	■ Tensile strength	5 N/cm
■ Colour	translucent	■ Type of liner	glassine
■ Total thickness	160 µm	■ Colour of liner	brown
■ Type of adhesive	synthetic rubber	■ Thickness of liner	70 µm
■ Elongation at break	2.5 %	■ Weight of liner	78 g/m²

Adhesion to

■ Steel (initial)	15.2 N/cm	■ PET (initial)	10.6 N/cm
■ ABS (initial)	11.8 N/cm	■ PP (initial)	8.9 N/cm
■ Aluminium (initial)	13.0 N/cm	■ PS (initial)	12.4 N/cm
■ PC (initial)	13.4 N/cm	■ PVC (initial)	11.7 N/cm
■ PE (initial)	9.0 N/cm		

Properties

■ Temperature resistance (short & long term)	80 & 40 °C	■ Static shear resistance at 23°C	++
■ Tack	+	■ Static shear resistance at 40°C	+
■ Humidity resistance	+	■ Ageing resistance (UV)	o

Evaluation across relevant tesa® assortment: ++ very good, + good, o medium, - low

tesa UK Ltd.

Yeomans Drive, Blakelands
Milton Keynes, Bucks MK 14 5LS
Phone: +44 (1) 908 211 333
Fax: +44 (1) 908 211 555
ukenquiry@tesa.com