


THESE DRAWINGS AND SPECIFICATIONS ARE THE SOLE PROPERTY OF I/O INTERCONNECT INC., U.S.A. AND SHALL NOT BE REPRODUCED, COPIED, OR USED IN ANY MANNER WITHOUT THE PRIOR WRITTEN CONSENT OF I/O INTERCONNECT INC. OR ITS AFFILIATED SUBSIDIARIES.



PI



CUSTOMER APPROVAL
ENGR. SIGN Math Lumer
DATE: 4-13-99

- NOTES: UNLESS OTHERWISE SPECIFIED.
1. TEST CABLE FOR ALL OPENS & SHORTS.
 2. PACKAGE CABLE ASSEMBLY INDIVIDUALLY IN PLASTIC BAG.
PACKAGE INDIVIDUAL BAG PER LOT NUMBER QUANTITIES.

ITEM	QTY	1 PC	MFG.	DESCRIPTION
2				MODULAR COIL CABLE, 26 AWG (7/34) BARE COPPER, 6 CONDUCTOR, UNSHIELDED, PVC JACKET, (SEE TABULATION BLOCK FOR COLOR).
1				CONNECTOR, MODULAR PLUG, 6 POSITION, 50U\"/>

CABLE ASSEMBLY PARTS LIST

466-146-525-D	121-610-022	14.0 FT (4.3 M)	44.0 IN (1117.6 MM)	WHITE
466-146-524-D	121-610-012	14.0 FT (4.3 M)	44.0 IN (1117.6 MM)	BLACK
466-146-523-D	121-610-002	14.0 FT (4.3 M)	44.0 IN (1117.6 MM)	SILVER SATIN
466-106-522-D	121-610-021	10.0 FT (3.0 M)	32.0 IN (812.8 MM)	WHITE
466-106-521-D	121-610-011	10.0 FT (3.0 M)	32.0 IN (812.8 MM)	BLACK
466-106-520-D	121-610-001	10.0 FT (3.0 M)	32.0 IN (812.8 MM)	SILVER SATIN
466-076-525-D	121-610-020	7.0 FT (2.1 M)	24.0 IN (609.6 MM)	WHITE
466-076-524-D	121-610-010	7.0 FT (2.1 M)	24.0 IN (609.6 MM)	BLACK
466-076-523-D	121-610-000	7.0 FT (2.1 M)	24.0 IN (609.6 MM)	SILVER SATIN
466-056-522-D	121-610-023	5.0 FT (1.5 M)	18.0 IN (457.2 MM)	WHITE
466-056-521-D	121-610-013	5.0 FT (1.5 M)	18.0 IN (457.2 MM)	BLACK
466-056-520-D	121-610-003	5.0 FT (1.5 M)	18.0 IN (457.2 MM)	SILVER SATIN
IDI PART NUMBER	IDI CABLE PART NUMBER	EXTENDED LENGTH "X"	RETRACTED LENGTH "R"	

TABULATION BLOCK

THIRD ANGLE PROJECTION

UNLESS OTHERWISE NOTED:
1) DIMENSIONS ARE IN INCHES (MILLIMETER)
2) TOLERANCES:
XXX ± 0.25 (6.35)

I/O INTERCONNECT

SANTA ANA, CALIFORNIA

TITLE: 6P6C COIL CABLE

TO OPEN END, CABLE ASSEMBLY

PART NO: 466-XX6-52X-D

DWG NO: 466-XX6-52X-D

CUSTOMER: DIGI KEY


REV: X2

SCALE: NONE


SHEET 1 OF 1

A		B		C		D		E		F		G		H	
DVG. NO.		ZONE		REV.		DESCRIPTION		DATE		APPROVED		E.V.		E.V.	
XX6-50X-D				X1		CUSTOMER APPROVAL		03/26/99		E.V.		03/29/99		E.V.	
				X2		ADD RETRACTED LENGTH									

THESE DRAWINGS AND SPECIFICATIONS ARE THE SOLE PROPERTY OF I/O INTERCONNECT INC. U.S.A. AND SHALL NOT BE REPRODUCED, COPIED, OR USED IN ANY MANNER WITHOUT THE PRIOR WRITTEN CONSENT OF I/O INTERCONNECT INC. OR ITS AFFILIATED SUBSIDIARIES.



P2



CUSTOMER APPROVAL
ENGR. SIGN Matt Lerner
DATE: 4-13-99

NOTES: UNLESS OTHERWISE SPECIFIED.

1. TEST CABLE FOR ALL OPENS & SHORTS.

2. PACKAGE CABLE ASSEMBLY INDIVIDUALLY IN PLASTIC BAG.
PACKAGE INDIVIDUAL BAG PER LOT NUMBER QUANTITIES.


TABULATION BLOCK

466-146-503-D	121-610-022	14.0 FT (4.3 M)	44.0 IN (1117.6 MM)	WHITE
466-146-504-D	121-610-012	14.0 FT (4.3 M)	44.0 IN (1117.6 MM)	BLACK
466-146-503-D	121-610-002	14.0 FT (4.3 M)	44.0 IN (1117.6 MM)	SILVER SATIN
466-106-502-D	121-610-021	10.0 FT (3.0 M)	32.0 IN (812.8 MM)	WHITE
466-106-501-D	121-610-011	10.0 FT (3.0 M)	32.0 IN (812.8 MM)	BLACK
466-106-500-D	121-610-001	10.0 FT (3.0 M)	32.0 IN (812.8 MM)	SILVER SATIN
466-076-503-D	121-610-020	7.0 FT (2.1 M)	24.0 IN (609.6 MM)	WHITE
466-076-504-D	121-610-010	7.0 FT (2.1 M)	24.0 IN (609.6 MM)	BLACK
466-076-503-D	121-610-000	7.0 FT (2.1 M)	24.0 IN (609.6 MM)	SILVER SATIN
466-056-502-D	121-610-023	5.0 FT (1.5 M)	18.0 IN (457.2 MM)	WHITE
466-056-501-D	121-610-013	5.0 FT (1.5 M)	18.0 IN (457.2 MM)	BLACK
466-056-500-D	121-610-003	5.0 FT (1.5 M)	18.0 IN (457.2 MM)	SILVER SATIN
IOI PART NUMBER	IOI CABLE PART NUMBER	EXTENDED LENGTH "X"	RETRACTED LENGTH "R"	COLOR

THIRD ANGLE PROJECTION



UNLESS OTHERWISE NOTED
1) DIMENSIONS ARE IN INCHES (MILLIMETER)
2) TOLERANCES:
XXX ± 0.25 (6.35)




TITLE		6962/696C COIL CABLE,	
REVERSE STYLE, CABLE ASSEMBLY			
PART NO.	466-XX6-50X-D		
DWG NO.	466-XX6-50X-D		
CUSTOMER	DIGI KEY		
REV. X2			
SCALE	NONE	SHEET 1 OF 1	

CABLE ASSEMBLY PARTS LIST


ITEM	QTY	WFG.	IOI PART NO.	DESCRIPTION
2	2 PCS	IOI	SEE "TABULATION BLOCK"	MODULAR COIL CABLE, 26 AVG (7/34) BARE COPPER, 6CONDUCTOR, UNSHIELDED, PVC JACKET, (SEE TABULATION BLOCK FOR COLOR).
1	2 PCS	IOI	325-661-50X	CONNECTOR, MODULAR PLUG, 6 POSITION, 6 CONDUCTOR, 50U" AU, FLAT TYPE EXIT.

A		B	C	D	E	F	G	H			
THESE DRAWINGS AND SPECIFICATIONS ARE THE SOLE PROPERTY OF I/O INTERCONNECT INC., U.S.A. AND SHALL NOT BE REPRODUCED, COPIED, OR USED IN ANY MANNER WITHOUT THE PRIOR WRITTEN CONSENT OF I/O INTERCONNECT INC. OR ITS AFFILIATED SUBSIDIARIES.											
		DVG. NO.		ZONE		REV.		DESCRIPTION		DATE	
		XX6-SIX-D				X1		CUSTOMER APPROVAL		03/26/99	
						X2		ADD RETRACTED LENGTH		03/29/99	

THESE DRAWINGS AND SPECIFICATIONS ARE THE SOLE PROPERTY OF I/O INTERCONNECT INC. NO PART SHALL BE REPRODUCED, COPIED, OR USED IN ANY MANNER WITHOUT THE PRIOR WRITTEN CONSENT OF I/O INTERCONNECT INC. OR ITS AFFILIATED SUBSIDIARIES.



P2



CUSTOMER APPROVAL
ENGR. SIGN *Math Yarnes*
DATE: 4-13-99

- NOTES: UNLESS OTHERWISE SPECIFIED.
1. TEST CABLE FOR ALL OPENS & SHORTS.
 2. PACKAGE CABLE ASSEMBLY INDIVIDUALLY IN PLASTIC BAG. PACKAGE INDIVIDUAL BAG PER LOT NUMBER QUANTITIES.

WIRE DIAGRAM

P1	P2
1	WHITE
2	BLACK
3	RED
4	GREEN
5	YELLOW
6	BLUE

466-146-S15-D	121-610-022	14.0 FT (4.3 M)	44.0 IN (1117.6 MM)	WHITE
466-146-S14-D	121-610-012	14.0 FT (4.3 M)	44.0 IN (1117.6 MM)	BLACK
466-146-S13-D	121-610-002	14.0 FT (4.3 M)	44.0 IN (1117.6 MM)	SILVER SATIN
466-106-S12-D	121-610-021	10.0 FT (3.0 M)	32.0 IN (812.8 MM)	WHITE
466-106-S11-D	121-610-011	10.0 FT (3.0 M)	32.0 IN (812.8 MM)	BLACK
466-106-S10-D	121-610-001	10.0 FT (3.0 M)	32.0 IN (812.8 MM)	SILVER SATIN
466-076-S15-D	121-610-020	7.0 FT (2.1 M)	24.0 IN (609.6 MM)	WHITE
466-076-S14-D	121-610-010	7.0 FT (2.1 M)	24.0 IN (609.6 MM)	BLACK
466-076-S13-D	121-610-000	7.0 FT (2.1 M)	24.0 IN (609.6 MM)	SILVER SATIN
466-056-S12-D	121-610-023	5.0 FT (1.5 M)	18.0 IN (457.2 MM)	WHITE
466-056-S11-D	121-610-013	5.0 FT (1.5 M)	18.0 IN (457.2 MM)	BLACK
466-056-S10-D	121-610-003	5.0 FT (1.5 M)	18.0 IN (457.2 MM)	SILVER SATIN
IOI PART NUMBER	IOI CABLE PART NUMBER	EXTENDED LENGTH "X"	RETRACTED LENGTH "R"	

TABULATION BLOCK


				I/O INTERCONNECT SANTA ANA, CALIFORNIA	
THIRD ANGLE PROJECTION		UNLESS OTHERWISE NOTED, DIMENSIONS ARE IN INCHES (MILLIMETER)		6P6C/6P6C COIL CABLE, STANDARD STYLE, CABLE ASSEMBLY	
1) DIMENSIONS ARE IN INCHES (MILLIMETER)		2) TOLERANCES: XXX ± 0.25 (6.35)		PART NO. 466-S16-SIX-D DWG NO. 466-S16-SIX-D CUSTOMER DIGI KEY SCALE NONE SHEET 1 OF 1	
CABLE ASSEMBLY PARTS LIST					
ITEM	QTY	MFG.	IOI PART NO.	DESCRIPTION	
2	2 PCS	SEE	325-661-SOX	MODULAR COIL CABLE, 26 AVG (7/34) BARE COPPER, 6 CONDUCTOR, UNSHIELDED, PVC JACKET, (SEE TABULATION BLOCK FOR COLOR).	
1	2 PCS	IOI	325-661-SOX	CONNECTOR, MODULAR PLUG, 6 POSITION, 6 CONDUCTOR, 50U" AU, FLAT TYPE EXIT.	

THESE DRAWINGS AND SPECIFICATIONS ARE THE SOLE PROPERTY OF I/O INTERCONNECT INC., U.S.A. AND SHALL NOT BE REPRODUCED, COPIED, OR USED IN ANY MANNER WITHOUT THE PRIOR WRITTEN CONSENT OF I/O INTERCONNECT INC. OR ITS AFFILIATED SUBSIDIARIES.

DWG. NO.	ZONE	REV.	DESCRIPTION	DATE	APPROVED
XX6-512-D		X1	CUSTOMER APPROVAL	03/24/99	E.V.

WIRE DIAGRAM

P1	P2
1	WHITE
2	BLACK
3	RED
4	GREEN
5	YELLOW
6	BLUE



CUSTOMER APPROVAL
 ENGR. SIGN Matt Aemmer
 DATE: 4-12-99

- NOTES: UNLESS OTHERWISE SPECIFIED.
- CABLE TO BE BUNDLED AND TWIST TIED.
 - TEST CABLE FOR ALL OPENS & SHORTS.
 - PACKAGE CABLE ASSEMBLY INDIVIDUALLY IN PLASTIC BAG. PACKAGE INDIVIDUAL BAG PER LOT NUMBER QUANTITIES.

H1661-25-ND
 H1661-14-ND
 H1661-07-ND

466-256-512-D	25.0 FT ± 4.0 IN 762 M ± 101.6 MM
466-146-512-D	14.0 FT ± 3.0 IN 427 M ± 76.2 MM
466-076-512-D	7.0 FT ± 2.0 IN 213 M ± 50.8 MM

PART NUMBER
 I/O INTERCONNECT



LENGTH "X"

				I/O INTERCONNECT SANTA ANA, CALIFORNIA	
		TITLE 6P6C MODULAR, STANDARD STYLE, WHITE, CABLE ASSEMBLY			
THIRD ANGLE PROJECTION		PART NO. 466-XX6-512-D		REV. X1	
UNLESS OTHERWISE NOTED, DIMENSIONS ARE IN INCHES (MILLIMETER) TOLERANCES: XXX ± 0.25 (6.35)		PART NO. 466-XX6-512-D		REV. X1	
CUSTOMER APPROVAL		CUSTOMER APPROVAL		SCALE: NONE	
SHEET 1 OF 1		SHEET 1 OF 1		SHEET 1 OF 1	

ITEM	QTY	MFG.	DESCRIPTION
2	*X*	IOI	MODULAR CABLE, 26 AVG (7/34) BARE COPPER, 6 CONDUCTOR, UNSHIELDED, WHITE PVC.
1	2 PCS	IOI	CONNECTOR, MODULAR PLUG, 6 POSITION, 6 CONDUCTOR, 50u" Au, FLAT TYPE EXIT.
CABLE ASSEMBLY PARTS LIST			

A	B	C	D	E	F	G	H
REV. NO.	ZONE	REV.	DESCRIPTION	CUSTOMER APPROVAL	DATE	APPROVED	
XXG-510-D	XI				03/24/99	E.V.	

THESE DIMENSIONS AND SPECIFICATIONS ARE THE SOLE PROPERTY OF I/O INTERCONNECT INC. NO PART OF THIS DOCUMENT IS TO BE REPRODUCED OR TRANSMITTED IN ANY FORM OR BY ANY MEANS WITHOUT THE PRIOR WRITTEN CONSENT OF I/O INTERCONNECT INC. OR ITS AFFILIATED SUBSIDIARIES.



WIRE DIAGRAM

P1	P2
1	WHITE
2	BLACK
3	RED
4	GREEN
5	YELLOW
6	BLUE

CUSTOMER APPROVAL
ENGR. SIGN Math Farmer
DATE: 4-12-99

- NOTES: UNLESS OTHERWISE SPECIFIED.
1. CABLE TO BE BUNDLED AND TWIST TIED.
 2. TEST CABLE FOR ALL OPENS & SHORTS.
 3. PACKAGE CABLE ASSEMBLY INDIVIDUALLY IN PLASTIC BAG. PACKAGE INDIVIDUAL BAG PER LOT NUMBER QUANTITIES.

H1663-25-NB
H1663-14-NB
H1663-07-NB

466-256-510-D	25.0 FT ± 4.0 IN 7.62 M ± 101.6 MM
466-146-510-D	14.0 FT ± 3.0 IN 4.27 M ± 76.2 MM
466-076-510-D	7.0 FT ± 2.0 IN 2.13 M ± 50.8 MM
PART NUMBER	LENGTH "X"


I/O INTERCONNECT	
SANTA ANA, CALIFORNIA	
REV. NO.	466-XXG-510-D
PART NO.	466-XXG-510-D
DATE	03/24/99
SCALE	1 OF 1

MODULAR CABLE, 26 AVG (7/34) BARE COPPER, 6 CONDUCTOR, UNSHIELDED, SILVER SATIN PVC.

CONNECTOR, MODULAR PLUG, 6 POSITION, 6 CONDUCTOR, 50u" Au, FLAT TYPE EXIT.

CABLE ASSEMBLY PARTS LIST

ITEM	QTY	MFG.	IOI PART NO.	DESCRIPTION
1	2 PCS	IOI	325-661-50X	CONNECTOR, MODULAR PLUG, 6 POSITION, 6 CONDUCTOR, 50u" Au, FLAT TYPE EXIT.
2	"X"	IOI	120-610-000	MODULAR CABLE, 26 AVG (7/34) BARE COPPER, 6 CONDUCTOR, UNSHIELDED, SILVER SATIN PVC.



ITEM	QTY	MFG.	IOI PART NO.	DESCRIPTION
2	1	IOI	120-610-010	MODULAR CABLE, 26 AVG (7/34) BARE COPPER, 6 CONDUCTOR, UNSHIELDED, BLACK PVC.
1	2 PCS	IOI	325-661-50X	CONNECTOR, MODULAR PLUG, 6 POSITION, 6 CONDUCTOR, 50u" Au, FLAT TYPE EXIT.


ITEM	QTY	MFG.	IOI PART NO.	DESCRIPTION
2	1	IOI	120-610-010	MODULAR CABLE, 26 AVG (7/34) BARE COPPER, 6 CONDUCTOR, UNSHIELDED, BLACK PVC.
1	2 PCS	IOI	325-661-50X	CONNECTOR, MODULAR PLUG, 6 POSITION, 6 CONDUCTOR, 50u" Au, FLAT TYPE EXIT.

ITEM	QTY	MFG.	IOI PART NO.	DESCRIPTION
2	1	IOI	120-610-010	MODULAR CABLE, 26 AVG (7/34) BARE COPPER, 6 CONDUCTOR, UNSHIELDED, BLACK PVC.
1	2 PCS	IOI	325-661-50X	CONNECTOR, MODULAR PLUG, 6 POSITION, 6 CONDUCTOR, 50u" Au, FLAT TYPE EXIT.

ITEM	QTY	MFG.	IOI PART NO.	DESCRIPTION
2	1	IOI	120-610-010	MODULAR CABLE, 26 AVG (7/34) BARE COPPER, 6 CONDUCTOR, UNSHIELDED, BLACK PVC.
1	2 PCS	IOI	325-661-50X	CONNECTOR, MODULAR PLUG, 6 POSITION, 6 CONDUCTOR, 50u" Au, FLAT TYPE EXIT.

A		B	C	D	E	F	G	H
DWG. NO.		ZONE	REV.	DESCRIPTION	DATE	APPROVED		
XX6-500-D		X1		CUSTOMER APPROVAL	03/24/99	E.V.		

THESE DRAWINGS AND SPECIFICATIONS ARE THE SOLE PROPERTY OF I/O INTERCONNECT INC. NO PARTS OR SUBASSEMBLIES ARE TO BE REPRODUCED OR USED IN ANY MANNER WITHOUT THE WRITTEN CONSENT OF I/O INTERCONNECT INC. OR ITS AFFILIATED SUBSIDIARIES.



WIRE DIAGRAM

P1	P2
1	WHITE
2	BLACK
3	RED
4	GREEN
5	YELLOW
6	BLUE

CUSTOMER APPROVAL


ENGR. SIGN Math J. Jemur
DATE: 4-12-99

NOTES: UNLESS OTHERWISE SPECIFIED.

1. CABLE TO BE BUNDLED AND TWIST TIED.
2. TEST CABLE FOR ALL OPENS & SHORTS.
3. PACKAGE CABLE ASSEMBLY INDIVIDUALLY IN PLASTIC BAG. PACKAGE INDIVIDUAL BAG PER LOT NUMBER QUANTITIES.

H2663-25-ND
H2663-14-ND
H2663-07-ND

466-256-500-D	25.0 FT ± 4.0 IN 7.62 M ± 101.6 MM
466-146-500-D	14.0 FT ± 3.0 IN 4.27 M ± 76.2 MM
466-076-500-D	7.0 FT ± 2.0 IN 2.13 M ± 50.8 MM
PART NUMBER	LENGTH "X"
I/O INTERCONNECT	



THIRD ANGLE PROJECTION

ITEM	QTY	ITEM	QTY
2	101	120-610-000	
1	2 PCS	101	
ITEM	QTY	MFG.	IOI

MODULAR CABLE, 26 AWG (7/34) BARE COPPER, 6 CONDUCTOR, UNSHIELDED, SILVER SATIN PVC.	
CONNECTOR, MODULAR PLUG, 6 POSITION, 6 CONDUCTOR, 50u" AU, FLAT TYPE EXIT.	
DESCRIPTION	

CABLE ASSEMBLY PARTS LIST

UNLESS OTHERWISE NOTED
1) DIMENSIONS ARE IN INCHES (MILLIMETER)
2) TOLERANCES
XXX ± 0.25 (6.35)

SCALE	NONE	SHEET	1	OF	1
-------	------	-------	---	----	---

DATE	03/24/99
------	----------

REV.	X1
------	----

REV.	X1
------	----

REV.	X1
------	----

REV.	X1
------	----

REV.	X1
------	----

REV.	X1
------	----



REV.	X1
------	----

REV.	X1
------	----

A	B	C	D	E	F	G	H
THESE DRAWINGS AND SPECIFICATIONS ARE THE SOLE PROPERTY OF I/O INTERCONNECT INC. NO PARTS OR SPECIFICATIONS MAY BE REPRODUCED OR USED IN ANY MANNER WITHOUT THE WRITTEN CONSENT OF I/O INTERCONNECT INC. OR ITS AFFILIATED SUBSIDIARIES.					DWG. NO. XX6-522-D	ZONE X1	REV. X1
					DESCRIPTION CUSTOMER APPROVAL		DATE 03/24/99
							APPROVED E.V.

WIRE DIAGRAM

PI	OPEN END
1	WHITE
2	BLACK
3	RED
4	GREEN
5	YELLOW
6	BLUE



CUSTOMER APPROVAL
ENGR. SIGN Math Thomas
DATE: 4-12-99

- NOTES: UNLESS OTHERWISE SPECIFIED.
1. CABLE TO BE BUNDLED AND TWIST TIED.
 2. TEST CABLE FOR ALL OPENS & SHORTS.
 3. PACKAGE CABLE ASSEMBLY INDIVIDUALLY IN PLASTIC BAG. PACKAGE INDIVIDUAL BAG PER LOT NUMBER QUANTITIES.

H3661-25-ND
H3661-14-ND
H3661-07-ND

466-256-522-D	25.0 FT ± 4.0 IN 7.62 M ± 101.6 MM
466-146-522-D	14.0 FT ± 3.0 IN 4.27 M ± 76.2 MM
466-076-522-D	7.0 FT ± 2.0 IN 2.13 M ± 50.8 MM
PART NUMBER	LENGTH "X"

I/O INTERCONNECT			
SANTA ANA, CALIFORNIA			
THIRD ANGLE PROJECTION	UNLESS OTHERWISE NOTED 1) DIMENSIONS ARE IN INCHES (MILLIMETER) 2) TOLERANCES: XXX ± 0.25 (6.35)		
2	"X"	101	120-610-020
1	1 PC	101	325-661-50X
ITEM	QTY	MFG.	101 PART NO.
CABLE ASSEMBLY PARTS LIST			
MODULAR CABLE, 26 AWG (7/34) BARE COPPER, 6 CONDUCTOR, UNSHIELDED, WHITE PVC.			
CONNECTOR, MODULAR PLUG, 6 POSITION, 6 CONDUCTOR, 50U" AU, FLAT TYPE EXIT.			
DESCRIPTION			
SCALE: NONE			
SHEET 1 OF 1			

1

2

3

4

5

6

WIRE DIAGRAM

P1

1 WHITE

2 BLACK

3 RED

4 GREEN

5 YELLOW

6 BLUE

OPEN END



CUSTOMER APPROVAL
ENGR. SIGN Mark Thomas
DATE: 4-12-99

- NOTES: UNLESS OTHERWISE SPECIFIED.
- CABLE TO BE BUNDLED AND TWIST TIED.
 - TEST CABLE FOR ALL OPENS & SHORTS.
 - PACKAGE CABLE ASSEMBLY INDIVIDUALLY IN PLASTIC BAG. PACKAGE INDIVIDUAL BAG PER LOT NUMBER QUANTITIES.

2	"X"	101	120-610-010	MODULAR CABLE, 26 AWG (7/34) BARE COPPER, 6 CONDUCTOR, UNSHIELDED, BLACK PVC.
1	1 PC	101	325-661-50X	CONNECTOR, MODULAR PLUG, 6 POSITION, 6 CONDUCTOR, 50U" AU, FLAT TYPE EXIT.
ITEM	QTY	MFG.	IOI PART NO.	DESCRIPTION
CABLE ASSEMBLY PARTS LIST				

466-256-521-D	25.0 FT ± 4.0 IN 762 M ± 101.6 MM
466-146-521-D	14.0 FT ± 3.0 IN 427 M ± 76.2 MM
466-076-521-D	7.0 FT ± 2.0 IN 213 M ± 50.8 MM
PART NUMBER	LENGTH "X"

THIRD ANGLE PROJECTION

UNLESS OTHERWISE NOTED
1) DIMENSIONS ARE IN INCHES (MILLIMETER)
2) TOLERANCES:
XXX ± 0.25 (6.35)

I/O INTERCONNECT

SANTA ANA, CALIFORNIA

6P6C MODULAR, TO OPEN END, BLACK, CABLE ASSEMBLY

PART NO: 466-XX6-521-D

DWG NO: 466-XX6-521-D

CUSTOMER: 0101 KEY

REV: X1

SCALE: NONE

SHEET 1 OF 1

