

Color-Keyed®

Long Barrel Aluminum Lug

T&B Catalog Number:

60256

UPC Number:

78621060256

Status:

Active

Description:

Aluminum Two-Hole Lug - Straight Long Barrel - max 35KV, 250 kcmil Wire, 1/2" Bolt Size, 1 3/4" Hole Spacing, Tin Plated Blind End, Red 71H

General

Material	Aluminum
Finish	Tin Plated
Wire Size	250 kcmil
Number of Studs	2
Stud Size	1/2
Bolt Hole Spacing	1 3/4
Tongue Angle	Straight
Barrel Length	Long
Barrel Shape	Standard
Tongue Width	Standard
Peep Hole	N
Marking	Standard
Hole Shape	Round
Die Color	Red
Die Code	71H

Dimension Information

A (inches)	5.8
B (inches)	3
C (inches)	1.29
D (inches)	.27
E (inches)	.92
F (inches)	.5
G (inches)	1.75

Specifications

Voltage Rating	600V to 35KV
----------------	--------------

Tooling

Connector & Tooling Chart	Available on Website
---------------------------	----------------------


Packaging

T&B Order Multiple	5
T&B Inner Pack	5
Package in Units	50
T&B Sold in UOM	Each
T&B Weight Per UOM	19.7 lbs. per 100

Application Support

T&B Sales Drawings	wsd-000581
T&B Instruction Sheets	ta00880-tb2
Overview	Available on Website

Notes



Dimensions given for reference only. Dimensions may vary up to +/- .030.

Certifications

RoHS Compliance Yes

Certifications



File Nbr:
E9809

For further technical assistance, please contact us...

Thomas & Betts - USA
8155 T&B Blvd.
Memphis, TN 38125
www.tnb.com

T&B Technical Support
MS 3B-50
8155 T&B Blvd.
Memphis, TN 38125

Hours: 7AM - 6PM CDT
Monday-Friday
Phone: (888) 862-3289
Fax: (901) 252-1321
Email: techsupport@tnb.com