

TM-238 TM-239 Sealing Gasket



Characteristic

- (1) Excellent on weather-resistance, cold and heat-resistance, chemical-resistance, acid and alkali.
- (2) No deformation by its structure, small compressive stress.
- (3) Easy to compress.
- (4) Excellent waterproof performance for gaps between rough surfaces and for structure with temperature difference, since it follows the structure flexibly.
- (5) No chemical substance shall come out from the foam while it is heated or compressed.
- (6) Light weight, specific gravity 0.15, and no welding between foams, it is easy to install and store.

Application

Electric devices / Houses / Facility devices / Vessels / Vehicles / Automobiles / Construction and civil engineering uses, etc.

Specification

- Heat-resistance ——— -20°C~100°C
- Chemical-resistance ——— Excellent on acid-resistance and alkali-resistance
- Waterproofing ——— Waterproof at 70% and more compression.
- Foam ——— Continuous foaming
- Standard Size ——— Thickness: ——— 5mm to 25mm
Width: ——— 10mm to 30mm with 5mm step
Color: ——— Two types, black and gray

Note

1. Dirt and moisture on the surface to be fixed should be removed before fixing.
2. Adhesive agent should not be used for jointing. It may lower the dustproof and waterproof performances.


How To Order

TM-238 - 5 - 10
Model No (Black) Thickness width

And quantity you need

- Ask for a custom made product.

Rapping product: Production can be made for the size within 800mm and less square.



■Size List (Black:TM-238, Gray:TM-239)

Product No.	A	B	TM-238	TM-239
			Code No.	Code No.
5-10	5	10	6151	6181
5-15		15	6152	6182
5-20		20	6153	6183
5-25		25	6154	6184
5-30		30	6155	6185
8-10	8	10	6156	6186
8-15		15	6157	6187
8-20		20	6158	6188
8-25		25	6159	6189
8-30	10	30	6160	6190
10-10		10	6161	6191
10-15		15	6162	6192
10-20		20	6163	6193
10-25		25	6164	6194
10-30	15	30	6165	6195
15-10		10	6166	6196
15-15		15	6167	6197
15-20		20	6168	6198
15-25		25	6169	6199
15-30	20	30	6170	6200
20-10		10	6171	6201
20-15		15	6172	6202
20-20		20	6173	6203
20-25		25	6174	6204
20-30	25	30	6175	6205
25-10		10	6176	※ 6206
25-15		15	6177	※ 6207
25-20		20	6178	※ 6208
25-25		25	6179	※ 6209
25-30	30	30	6180	※ 6210

A size for ※marked products are made by adhesion of 20mm width product and 5mm width product.

