

New Products

Category 6 Shielded Component Compliant Plug

SS-39200-011 – Plug with Snag-less Strain Relief

- Designed for the highest reliability shield connection
- Wire loading bar for ease of assembly
- One step termination using tool kit 2980075-01
- Designed for cable up to .248" diameter
- Consult factory for terminations of larger cable diameters



Category 6 Component Compliant Plug

SS-39100-008 – Plug with Snag-less Strain Relief



- Patented strain relief design for high performance
- Built in slim profile snag-less strain relief for use in high density plug in equipment
- Designed for cable up to .230" in diameter
- Use termination tool kit 2990009-01

Category 5E Plug and Snag-less Slim Profile Strain Relief

SS-37000-007 – Plug 450-034 – Strain Relief

- Staggered contact design for Cat5E performance
- Use termination tool kit 2990003-01
- Clear boot designed for use in high density plug in equipment
- Designed for cable up to .224" diameter
- Plug can be used without strain relief



Category 5E Shielded Plug

SS-37200-028 – Plug

- Staggered contact design for Cat5E performance
- Use termination tool kit 2990003-01
- Single piece design with three grounding tabs for a reliable shield connection

Bel Stewart Connector

11118 Susquehanna Trail S.
Glen Rock PA 17327
PH 717-235-7512

www.stewartconnector.com

Anixter

PH 800-ANIXTER
www.anixter.com

L-com

PH 800-350-5266
www.L-com.com

Modular Plug Quick Reference

Part Number Packaged 25 Pieces Per Bag	Part Number Bulk Packaged	Description	Performance	AWG	Maximum Cable OD	Crimp Tool / Die Set Included	Individual Die Set
940-SP-3046-B25	940-SP-3046	6-Position 4-Conductor Solid or Stranded Conductor		24/26/28	.103"	2990002-01	2990005-01
940-SP-3066-B25	940-SP-3066	6-Position 6-Conductor Solid or Stranded Conductor		24/26/28	.103"	2990002-01	2990005-01
940-SP-3088-B25	940-SP-3088	8-Position 8-Conductor Solid or Stranded Conductor		24/26	.190"	2990003-01	2990006-01
SS-30800-064	940-SP-3088R-A133	8-Position 8-Conductor Solid or Stranded Conductor	Cat5/T1	24/26	.230"	2990003-01	2990006-01
SS-37000-006	SS-37000-002	8-Position 8-Conductor Solid or Stranded Conductor	Cat5E	24/26	.230"	2990003-01	2990006-01
SS-37200-032	SS-37200-028	Shielded 8-Position 8-Conductor Solid or Stranded Conductor	Cat5E	24/26	.230"	2990003-01	2990006-01
SS-39100-017	SS-39100-008	8-Position 8-Conductor Solid or Stranded Conductor Includes Snagless Strain Relief Boot	Cat6 Component Compliant	24/26	.230"	2990009-01	2990010-01
SS-39100-006	SS-39100-004	8-Position 8-Conductor Solid or Stranded Conductor	Cat6 Channel Compliant	24/26	.230"	2990003-01	2990006-01
SS-39200-014	SS-39200-011	Shielded 8-Position 8-Conductor Solid or Stranded Conductor Includes Snagless Strain Relief Boot	Cat6 Component Compliant	24/26	.232-.248"	2980075-01	
450-011-B25	450-011	Black RJ45 Snagless Boot					
450-012-B25	450-012	Dark Grey RJ45 Snagless Boot					
450-013-B25	450-013	Yellow RJ45 Snagless Boot					
450-014-B25	450-014	Green RJ45 Snagless Boot					
450-015-B25	450-015	Blue RJ45 Snagless Boot					
450-016-B25	450-016	Light Grey RJ45 Snagless Boot					
450-017-B25	450-017	Purple RJ45 Snagless Boot					
450-018-B25	450-018	White RJ45 Snagless Boot					
450-019-B25	450-019	Red RJ45 Snagless Boot					

- Consult factory for high volume termination equipment options

MADE IN THE USA