


(1.00 mm) .0394"

**BKT, BKS SERIES**

POLARIZED MICRO HEADER & SOCKET

SPECIFICATIONS

For complete specifications and recommended PCB layouts see www.samtec.com?BKT or www.samtec.com?BKS

Insulator Material:
Liquid Crystal Polymer

Terminal Material:
Phosphor Bronze

Plating:

Au or Sn over
50 μ " (1.27 μ m) Ni

Current Rating:

2.8 A per pin

(2 pins powered)

Operating Temp Range:

-55 °C to +125 °C

Insertion Depth:

(1.40 mm) .055" minimum

Normal Force:

40 grams (0.39 N) average

Max Cycles:

100 with 10 μ " (0.25 μ m) Au

RoHS Compliant:

Yes

PROCESSING

Lead-Free Solderable:

Yes

SMT Lead Coplanarity:


(0.10 mm) .004" max

RECOGNITIONS

For complete scope of recognitions see www.samtec.com/quality



APPLICATIONS



BKT LEAD STYLE	MATED HEIGHT*
-01	(4.14) .163
-02	(4.50) .177
-03	(5.00) .197
-04	(6.00) .236
-05	(7.00) .276

*Processing conditions will affect mated height.

TIGER CLAW
CONTACT

Note:
Some sizes, styles and options are non-standard, non-returnable.

BKT	1	NO. OF POSITIONS	BODY STYLE	PLATING OPTION	V	OPTIONS
		07 thru 69 (Odd lead counts only)	Specify BODY STYLE from chart	-F = Gold flash on post, Matte Tin on tail -L = 10 μ " (0.25 μ m) Gold on post, Matte Tin on tail		-S = Shrouded (15 positions minimum) -A = Alignment Pin (Metal or plastic at Samtec discretion) (13 positions minimum) -P = Pick & Place Pad (13 positions minimum) -TR = Tape & Reel Packaging -FR = Full Reel Tape & Reel (must order max. quantity per reel; Contact Samtec for quantity breaks)

-A OPTION

-P OPTION

-S OPTION

BODY STYLE	A	B	BOARD SPACE (Mated with BKS)
-01	(1.93) .076	(3.91) .154	(4.14) .163
-02	(2.29) .090	(4.27) .168	(4.50) .177
-03	(2.79) .110	(4.78) .188	(5.00) .197
-04	(3.78) .149	(5.77) .227	(6.00) .236
-05	(4.80) .189	(6.78) .267	(7.00) .276

BKS	1	NO. OF POSITIONS	01	PLATING OPTION	V	OPTIONS
		07 thru 69 (07 positions available with -TR only)		-F =Pre-plated Gold flash on contact, Matte Tin on tail -L =Pre-plated 10 μ " (0.25 μ m) Gold contact, Matte Tin on tail		-A =Alignment Pin (Metal or plastic at Samtec discretion) (11 positions minimum) -P =Pick & Place Pad (13 positions minimum) Not always necessary for auto placement. -TR =Tape & Reel Packaging -FR =Full Reel Tape & Reel (must order max. quantity per reel; Contact Samtec for quantity breaks)

-P OPTION

-A OPTION