






REV.	DATE	DESCRIPTION
NC	09/27/06	INITIAL RELEASE



RECOMMENDED CABLE
STRIPPING DIMS.



NOTE:
1. CRIMPED FERRULE HEX CRIMP SIZE .213"
2. CONTACT PIN TO SOLDER

8					UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN MILLIMETERS. DIMENSIONS IN [] ARE IN INCHES AND FOR CUSTOMER REFERENCE ONLY. UNLESS OTHERWISE SPECIFIED TOLERANCES FOR MILLIMETERS ARE: 0.5 – 8mm ± 0.20mm 8 – 30mm ± 0.40mm 30 – 120mm ± 0.50mm UNLESS OTHERWISE SPECIFIED TOLERANCES FOR INCHES ARE: .020 – .315 = ± 0.007" .315 – 1.180 = ± 0.015" 1.180 – 4.724 = ± 0.020" DO NOT SCALE DRAWING	APPROVALS	DATE	Amphenol Connex					
7						DRAWN	G.R.S.						09/27/06
6						CHECKED			PART DESCRIPTION SMA PANEL CRIMP JACK (FOR RG-58/U CABLE)				
5						ISSUED							
4	FERRULE	COPPER	GOLD	1		SHEET	1 OF 1		PART NO. 132120				
3	CONTACT PIN	BER. COPPER	GOLD	1									
2	INSULATOR	TEFLON	NATURAL	1					DWG. NO. 132120.DWG REV. NC SIZE A SCALE NA				
1	BODY	BRASS	GOLD	1									
DESCRIPTION MATERIAL FINISH QTY													
							C:/132/132120.DWG						