

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

130006-0279

Status:

Active

Overview:

Brad® Mini-Change® Connectors

Description:

Mini-Change® A-Size Single-Ended Cordset, 3 Poles, Female (Straight) to Pigtail, STOOW Cable, 1.83m Length



image - Reference only

Series

Documents:

[Drawing \(PDF\)](#)

[RoHS Certificate of Compliance \(PDF\)](#)

Agency Certification

CSA

LR6837

UL

E152210

General

Product Family

Industrial Cordsets

Series

130006

Comments

A-Size (7/8" - 16 UN-2B)

Connector End A

Mini-Change®

Connector End B

Pigtail

IP Rating

IP67

NEMA Rating

NEMA 6

Overview

Brad® Mini-Change® Connectors

Product Name

Mini-Change®

Type

Single Ended

UPC

78678843019

Physical

Cable Diameter

10.41mm (.410")

Cable Length

1.83m

Color - Cable Jacket

Yellow

Coupling Style

Threaded

Gender

Female-Pigtail

Keyway

Single

LED Indicator

No

Material - Cable Jacket

PVC

Material - Connector Body

PVC

Material - Contact

Brass

Material - Coupling Nut

Black Epoxy Coated Zinc

Material - Plating Mating

Gold over Nickel

Orientation

Straight

Poles

3

Temperature Range - Operating

-20°C to +105°C

Wire Size AWG

16

Wire/Cable Type

STOOW

Electrical

Current - Maximum per Contact

13A

Voltage - Maximum

600V

Material Info

Old Part Number

103000A02F060

Reference - Drawing Numbers

Sales Drawing

SD-130006-020

EU RoHS

RoHS Compliant by
Exemption
REACH SVHC
Not Reviewed
Low-Halogen Status
Not Reviewed

China RoHS



Need more information on product
environmental compliance?

Email productcompliance@molex.com
For a multiple part number RoHS Certificate of
Compliance, [click here](#)

Please visit the [Contact Us](#) section for any
non-product compliance questions.

Search Parts in this Series
130006Series

This document was generated on 07/02/2013

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION