


THIS DRAWING IS UNPUBLISHED.		RELEASED FOR PUBLICATION		- .N/A .	
© COPYRIGHT	N/A	BY TYCO ELECTRONICS CORPORATION.		ALL RIGHTS RESERVED.	
PART NO.	A △1	B △1	CAP COLOR	REMARKS	
447391-1	19.00 [482.6]	6.00 [152.4]	GREEN	△3	
447391-2	27.00 [685.8]	6.00 [152.4]	GREEN	△3	
447391-3	35.00 [889.0]	6.00 [152.4]	GREEN	△3	
447391-4	42.00 [1066.8]	6.00 [152.4]	GREEN	△3	
447391-5	51.00 [1295.4]	6.00 [152.4]	GREEN	△3	
447391-6	59.00 [1498.6]	6.00 [152.4]	GREEN	△3	
447391-7	67.00 [1701.8]	6.00 [152.4]	GREEN	△3	
5-447391-1	19.00 [482.6]	6.00 [152.4]	GREEN	△6	
5-447391-2	27.00 [685.8]	6.00 [152.4]	GREEN	△6	
5-447391-3	35.00 [889.0]	6.00 [152.4]	GREEN	△6	
5-447391-4	42.00 [1066.8]	6.00 [152.4]	GREEN	△6	
5-447391-5	51.00 [1295.4]	6.00 [152.4]	GREEN	△6	
5-447391-6	59.00 [1498.6]	6.00 [152.4]	GREEN	△6	
5-447391-7	67.00 [1701.8]	6.00 [152.4]	GREEN	△6	

LOC	DIST	REVISIONS				
DF	S0	P	LTR	DESCRIPTION	DATE	DWN
		F		REV PER ECO-05-002357	08-05	AA
						DE

- △1 TOLERANCE OF LEAD LENGTH:
UP TO 24 INCHES [609.6] = ±.12 [±3.0]
24 INCHES [609.6] & UP = ±1%
- △2 MARKED PER MIL-STD-130.
- △3 PIGTAIL IS SOLDER DIPPED.
4. TO MATE WITH AMP LGH-1
RECEPTACLE WITH .88 [22.3] BARREL DEPTH.
5. OPERATING VOLTAGE: 20 KVDC AT 0 TO 70,000 FEET,
-55°C TO 125°C.
- △6 INSULATION CUT, BUT NOT REMOVED.



THIS DRAWING IS A CONTROLLED DOCUMENT.			DWN T.SHUEY	24-SEP-90	tyco Electronics		Tyco Electronics Corporation								
			CHK D.EABY	25-SEP-90			Harrisburg, Pa 17105-3608								
DIMENSIONS:		TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD D.EABY	25-SEP-90	NAME		LEAD ASSY							
INCHES [mm]				PRODUCT SPEC				DBL END, SHIELDED & GLASS BRAID JACKET							
		0 PLC ± -		—		SIZE		CAGE CODE		DRAWING NO		RESTRICTED TO			
		1 PLC ± -													
		2 PLC ± .02 [0.5]													
		3 PLC ± -													
		4 PLC ± -													
ANGLES ± ±				APPLICATION SPEC											
				—											
MATERIAL		FINISH		WEIGHT		A2		00779		C=447391		—			
SEE CALLOUTS		SEE CALLOUTS		—		CUSTOMER DRAWING		SCALE		1:1		SHEET 1 of 1		REV F	