

Verteilereinbaugeräte GREEN ELECTRIC®

Devices for junction boxes GREEN ELECTRIC®



Artikelbezeichnung <i>Article description</i>		Bemessungsstrom <i>rated current</i>	Art.-Nr <i>Art.No.</i>	EAN-Code <i>EAN code</i>	BE <i>PUC</i>
 Leitungsschutzschalter MCB 1-polig <i>Miniature Circuit Breaker MCB 1-pole</i> 230/400 V AC bzw. 60 V DC In 6–40 A 10000 3 In 50–63 A 10000 B		6 A	7206.0000.3	4008224162630	12
		10 A	7210.0000.6	4008224162647	12
		13 A	7213.0000.5	4008224162654	12
		16 A	7216.0000.4	4008224162661	12
		20 A	7220.0000.7	4008224162678	12
		25 A	7225.0000.2	4008224162685	12
		32 A	7232.0000.4	4008224162692	12
		40 A	7240.0000.9	4008224162708	12
		50 A	7250.0000.0	4008224162715	12
		63 A	7263.0000.0	4008224162722	12
 Leitungsschutzschalter MCB 1-polig + N <i>Miniature Circuit Breaker MCB, 1-pole + N</i> 230 V AC bzw. 60 V DC In 6–40 A 10000 3 In 50–63 A 10000 B		6 A	7206.1000.0	4008224163231	6
		10 A	7210.1000.3	4008224163248	6
		13 A	7213.1000.2	4008224163255	6
		16 A	7216.1000.1	4008224163262	6
		20 A	7220.1000.4	4008224163279	6
		25 A	7225.1000.9	4008224163286	6
		32 A	7232.1000.1	4008224163309	6
		40 A	7240.1000.6	4008224163316	6
		50 A	7250.1000.7	4008224163323	6
		63 A	7263.1000.7	4008224163330	6
 Leitungsschutzschalter MCB 2-polig <i>Miniature Circuit Breaker MCB, 2-pole</i> 400 V AC bzw. 60 V DC In 6–40 A 10000 3 In 50–63 A 10000 B		6 A	7206.2000.7	4008224163460	6
		10 A	7210.2000.0	4008224163484	6
		13 A	7213.2000.9	4008224209687	6
		16 A	7216.2000.8	4008224163491	6
		20 A	7220.2000.1	4008224163507	6
		25 A	7225.2000.6	4008224163514	6
		32 A	7232.2000.8	4008224163521	6
		40 A	7240.2000.3	4008224163538	6
		50 A	7250.2000.4	4008224163545	6
		63 A	7263.2000.4	4008224163552	6
 Leitungsschutzschalter MCB 3-polig <i>Miniature Circuit Breaker MCB, 3-pole</i> 400 V AC bzw. 60 V DC In 6–40 A 10000 3 In 50–63 A 10000 B		6 A	7206.3000.4	4008224517546	4
		10 A	7210.3000.7	4008224163767	4
		13 A	7213.3000.6	4008224163774	4
		16 A	7216.3000.5	4008224163781	4
		20 A	7220.3000.8	4008224163798	4
		25 A	7225.3000.3	4008224163804	4
		32 A	7232.3000.5	4008224163811	4
		40 A	7240.3000.0	4008224163828	4
		50 A	7250.3000.1	4008224163835	4
		63 A	7263.3000.1	4008224163842	4
 Leitungsschutzschalter MCB 3-polig + N <i>Miniature Circuit Breaker MCB, 3-pole + N</i> 400 V AC bzw. 60 V DC In 6–40 A 10000 3 In 50–63 A 10000 B		6 A	7206.4000.1	4008224164047	3
		10 A	7210.4000.4	4008224164054	3
		13 A	7213.4000.3	4008224238038	3
		16 A	7216.4000.2	4008224164061	3
		20 A	7220.4000.5	4008224164078	3
		25 A	7225.4000.0	4008224164085	3
		32 A	7232.4000.2	4008224164092	3
		40 A	7240.4000.7	4008224164122	3
		50 A	7250.4000.8	4008224164139	3
		63 A	7263.4000.8	4008224164146	3
 Leitungsschutzschalter MCB 1-polig <i>Miniature Circuit Breaker MCB, 1-pole</i> 230/400 V AC In 0,5–4 A 10000 3 In 50–63 A 10000 C		0,5 A	7205.0100.1	4008224249836	12
		1 A	7201.0100.9	4008224249744	12
		2 A	7202.0100.2	4008224249775	12
		4 A	7204.0100.8	4008224249805	12
		6 A	7206.0100.4	4008224162760	12
		10 A	7210.0100.7	4008224162777	12
		13 A	7213.0100.6	4008224163002	12
		16 A	7216.0100.5	4008224163019	12
		20 A	7220.0100.8	4008224163026	12
		25 A	7225.0100.3	4008224163033	12
		32 A	7232.0100.5	4008224163040	12
		35 A	7235.0100.4	4008224250153	12
		40 A	7240.0100.0	4008224163125	12
		50 A	7250.0100.1	4008224163132	12
		63 A	7263.0100.1	4008224163149	12
 Leitungsschutzschalter MCB 1-polig + N <i>Miniature Circuit Breaker MCB, 1-pole+N</i> 230 V AC In 6–40 A 10000 3 In 50–63 A 10000 C		6 A	7206.1100.1	4008224163347	6
		10 A	7210.1100.4	4008224163354	6
		13 A	7213.1100.3	4008224238045	6
		16 A	7216.1100.2	4008224163361	6
		20 A	7220.1100.5	4008224163378	6
		25 A	7225.1100.0	4008224163385	6
		32 A	7232.1100.2	4008224163392	6
		40 A	7240.1100.7	4008224163408	6
		50 A	7250.1100.8	4008224163439	6
		63 A	7263.1100.8	4008224163453	6
 Leitungsschutzschalter MCB 2-polig <i>Miniature Circuit Breaker MCB, 2-pole</i> 400 V AC In 0,5–4 A 10000 3 In 50–63 A 10000 C		0,5 A	7205.2100.5	4008224249966	6
		1 A	7201.2100.3	4008224249751	6
		2 A	7202.2100.6	4008224249782	6
		4 A	7204.2100.2	4008224249812	6
		6 A	7206.2100.8	4008224163569	6
		10 A	7210.2100.1	4008224163576	6
		13 A	7213.2100.0	4008224209694	6
		16 A	7216.2100.9	4008224163583	6
		20 A	7220.2100.2	4008224163590	6
		25 A	7225.2100.7	4008224163606	6
		32 A	7232.2100.9	4008224163613	6
		40 A	7240.2100.4	4008224163620	6
		50 A	7250.2100.5	4008224163637	6
		63 A	7263.2100.5	4008224163644	6