

Type: DA10-NSxx/xxx serial



DA10-NS40/xxx-4

case 48 x 48 mm



DA10-NS40/xxx

case 48 x 24 mm



DA10-NS40/xxx-7

case 72 x 24 mm




resolution

article	display
DA10-NS30/xxx	□□□
DA10-NS40/xxx	□□□□


DA10-NSxx/Axx

screw - type terminal



DA10-NSxx/Dxx


screw - type terminal



programming

code number	display	description
0	Pr 0	0 0 0 1 2 baud rate 1200 baud 2 4 2400 baud 4 8 4800 baud 9 6 9600 baud
1	Pr 1	0 0 data bit 0= 7 Bit 1= 8 Bit 0 parity bit 0= without 1= with 0 parity 0= even 1= odd
2	Pr 2	0 0 STX/ETX 0= without 1= with 0 SOH 0= without 1= mit
3	Pr 3	0 0 address without 0 1 1. device 9 9 99. device
4	Pr 4	0 0 leading zeros 0= without 1= with 0 direction of write left → right 1 direction of write right → left
5	Pr 5	0 0 blank out from up 99 signs 9 9

case view



technical data

aux. supply:	18 - 35 VDC
power consumption :	max. 1,5 VA
display :	height 10,0 mm, LED red or green
temperature range :	-20 °C+65 °C
parallel gear change :	max. 32 devices
case :	DA10-NSxx/xxx: DA10-NSxx/xxx-4: DA10-NSxx/xxx-7:
mounting depth :	120 mm 120 mm 120 mm
panel cutout :	45(+0,6) x 22,2(+0,3)mm 45(+0,6) x 45(+0,6)mm 68(+0,7) x 22,2(+0,3)mm
bezel height :	5,25 mm 5,25 mm 5,25 mm

software- function


function	ASCII	description
segment test	\$0	segment test on (up to the next telegramm)
leading zeros	\$1	leading zeros displayed
zeros	\$2	leading zeros suppressed
blinking sign	\$3"28"	"28" is blinking
blinking display	\$4	blinking on
	\$5	blinking off
direction of write	\$6	left → right
	\$7	right → left

signs

Hex	20	2D	2E	30	31	32	33	34	35	36	37	38	39	3D	41	43	45	46	48	4C	50	55	5D	5F	62	63	64	68	6E	6F	72	75	78	7E
Digit	-	.	0	1	2	3	4	5	6	7	8	9	=	A	C	E	F	H	L	P	U	]	_	b	c	d	h	n	o	r	u	□	+	

unknown sign

DA10-NS□□□□□□□□



without	= 48 x 24 mm	4 = 48 x 48 mm	7 = 72 x 24 mm
R = red	G = green		
1 = 24VDC			
A = RS232C/V.24	D = RS422 / RS485		
30 = 3 digits	40 = 4 digits		

DA10-NS□□□□□□□□

GS Gebhardt & Schäfer Industrie-Elektronik GmbH

Moltkestraße 44a, D-42799 Leichlingen
Postfach 15 52, D-42786 Leichlingen
Tel. +49 (0) 21 75 / 89 91 30
Fax +49 (0) 21 75 / 89 91 39
Internet: <http://www.GS-GmbH.de>
E-Mail: info@GS-GmbH.de

Deutsche Bank 24
Konto-Nr. 851 085 100
BLZ 375 700 24
Kreissparkasse Köln
Konto-Nr. 031 200 61 45
BLZ 370 502 99

Foreign Payments:
Deutsche Bank 24
Account-No. 851 085 1
Bank Code 375 700 24
IBAN DE 81375700240008510851
S.W.I.F.T. DEUTDE33 375

Geschäftsführer:
Karlheinz Schäfer
Guido Gebhardt
USt.-Nr. DE 123713297
Amtsgericht Köln
HRB 48860