

Electromechanical Components
› Connectors
› Relays
› Touch Panels
› KVM Switches
› Thermal Printers
› Input Devices
› Wireless Modules
› WLAN
› Bluetooth
› WLAN & Bluetooth Combo
› Evaluation Boards
› Optical Modules
› DC/DC Converters

Bluetooth iOS module - Power Class 2

Part Number MBH7BTZ50

Status  Active

IC CSR BC4-External

Package FPC interconnect module with fixing holes and patterned antenna



We're Here to Help

How to Buy

- Sales contacts

- Stock check

Support Info

- Technical / sales support


Features

- Before using this module, please note that user must be a member of the Apple Inc.® Mfi licensing program (<https://developer.apple.com/programs/mfi/>)
- Bluetooth specification version 2.1 + EDR compliant
- Power Class 2 (+4dBm max.)
- Upper layer protocol stack (L2CAP, SDP, RFCOMM) and profiles (GAP, SPP) are embedded
- Receiver sensitivity: basic rate -87dBm typical
- Hardware interface: UART (9.6k ~1.382kbps)
- Software interface: simple proprietary command
- Operating temperature: -25 to +85 degrees C
- Supply voltage: 2.7 to 3.6VDC
- FPC/FFC connector
- Patterned antenna
- Bluetooth Qualified End Product: ID No: B016068 (SIG website:<https://www.bluetooth.org/tpg/listings.cfm>)
- 31.0 x 15.0 x 2.5mm
- FCC/IC/CE compliant
- RoHS compliant

Documentation

- Datasheet: n/a
- Specification: please contact Fujitsu
- Eval kit: n/a
- [Blockdiagram](#)
-

Blockdiagram



[Top of Page](#) 

Services & Solutions	Products	Help and Support	Most Popular	Country Selector
Business Services	Computing Products	Support & Downloads	FUJITSU Image Scanner	United States Change
Managed Infrastructure Services	Servers	Support for Fujitsu Scanners	Notebooks	
Fujitsu Retailing Solutions	Network Products	Notebooks & Tablet PCs	Store Technology	
Network Services	Semiconductors	Shop Fujitsu	PalmSecure®	
ASIC and Foundry Services	Components	How to Buy	UHF RFID Tag	

