






NOTES:

- MATERIALS AND FINISHES(PLATING THICKNESS IN MICRO-INCHES):
BODY - BRASS, NICKEL PLATING
CONTACT - BERYLLIUM COPPER, GOLD PLATING
INSULATOR - PTFE
- ELECTRICAL:
A. IMPEDANCE: 75 OHM
B. FREQUENCY RANGE: DC 0-1 GHz
C. VSWR(RETURN LOSS): 1.3 MAX.
D. DIELECTRIC WITHSTANDING VOLTAGE: 1000 VRMS, MIN.
- MECHANICAL:
A. DURABILITY: 500 CYCLES MIN.
B. TEMPERATURE RANGE: - 40°C to +155°C
- CRIMPED FERRULE
HEX CRIMP SIZE .178"
- CRIMPED CONTACT PIN
CONTACT PIN TO SOLDER

31-70331

REVISIONS

PART NO.	REV	DESCRIPTION	DATE	ECO	APPR
THIRD ANGLE PROJ.	A	RELEASE TO MFG.	08-Aug-06	46214	CISSY

RECOMMENDED
CABLE STRIPPING DIM'S

CUSTOMER OUTLINE DRAWING

ALL OTHER SHEETS ARE FOR INTERNAL USE ONLY

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN METRIC AND TOLERANCES ARE: 0.5 - 6mm ±0.1mm 6 - 30mm ±0.2mm 30 - 120mm ±0.3mm ANGLES ±1°	MATERIAL	DRAWN CISSY	DATE 08-Aug-06	TITLE MINI BNC CRIMP JACK (FOR RG-316/U, 174/U, 188A/U CABLE)	Amphenol RF		
					Danbury CT USA, Tainan Taiwan, Shenzhen China www.amphenolrf.com		
NOTICE - These drawings, specifications, or other data (1) are, and remain the property of Amphenol Corp. (2) must be returned upon request; and (3) are confidential and not to be disclosed to any person other than those to whom they are given by Amphenol Corp. The furnishing of these drawings, specifications, or other data by Amphenol Corp., or to any other person to anyone for any purpose is not to be regarded by implication or otherwise in any manner licensing, granting rights or permitting such holder or any other person to manufacture, use or sell any product, process or design, patented or otherwise, that may in any way be related to or disclosed by said drawings, specifications, or other data.	REFERENCE	APPROVED <i>[Signature]</i>	DATE 08-Aug-06	SCALE: 3/1	SHEET 1 OF 1	DRAWING NO. MNB6121A1-001-NT3G-75	
						ITEM NO. 316121AAB36NA7F	
FINISH	F:\DWG\MNB\6121A1\001\75\NT3GSZ	CAD FILE	DWG SIZE B	CODE ID 74868	REV A	PART NO. 31-70331	