



TW-16-06-T-D-500-100

TW SERIES

THROUGH-HOLE BOARD STACKERS

Choice of one through six rows

TW

NO. PINS PER ROW

02 thru 50

LEAD STYLE

Specify LEAD STYLE from chart below.

PLATING OPTION

-F
 = Gold flash on post, Matte Tin on tail

 -L
 = 10μ" (0,25 μm) Gold on post, Matte Tin on tail

 -T
 = Matte Tin

ROW OPTION

-S
 = Single Row

 -D
 = Double Row

 -T
 = Triple Row

 -Q
 = Four Row

 -5
 = Five Row

 -6
 = Six Row

STACKER HEIGHT

-"XXX"
 = Stacker Height in inches (0,13 mm) .005" increments
 Example: -250 = (6,35 mm) .250"

TAIL SPEC

-"XXX"
 = Tail Length in inches (0,13 mm) .005" increments
 Example: -150 = (3,81 mm) .150"

 -"XXX"
 = Polarized Position (Specify position to be removed)

LEAD STYLE	OAL
-01	(8,20) .323
-02	(9,60) .377
-03	(13,60) .535
-04	(14,10) .555
-05	(15,10) .594
-06	(17,10) .673
-07	(19,10) .751
-08	(21,10) .830
-09	(11,60) .456
-10	(15,60) .614
-11	(10,08) .397
-12	(28,19) 1.110

ROW OPTION	STACKER HEIGHT
-S, -D*, & -Q	(3.05) .120 MIN
-T -5 -6	(4.06) .160 MIN

*-D with stacker height greater than (4,06 mm) .160" will not have standoffs.