

Technical datasheet: FT-34.7G-2.9B1-474

Specifications:

Resonant Frequency	2.8kHz $\pm$ 0.5kHz
Max Resistance (Zr)	300 Ω
Capacitance	30000nF $\pm$ 30%nF

Dimensions:

Type B: (D: $\varnothing$ 34.7mm, d: $\varnothing$ 25.0mm, T: 0.50mm, t: 0.25mm)

