


Dimensions: mm (In.)

**Mechanical Specifications:**

- Mechanical Life: 50,000 make-and-break cycles.
- Operating Temperature: -30°C to 85°C

Electrical Specifications:

- Rating: 0.4 Volt-Amps (VA) max. @20V max (AC or DC)
- Contact Resistance: 20mΩmax. initial @ 2-4VDC 100mA
- Insulation Resistance: 1,000MΩmin.
- Dielectric Strength: 1,000 V RMS@ sea level

Materials:

- Case & Bushing: Glass filled nylon 66, flame retardant, heat stabilized
- Plunger: Thermoplastic polyester, with internal O-ring seal
- Switch Support: Brass or Steel, electrotin plate
- Contact: Gold plated copper alloy

Note:

- RoHS compliant by exemption

Sealed Sub-Miniature Pushbutton Switch

107-3021-EVX

Mountain
Switch

Available from Mouser Electronics

www.mouser.com 1-800-346-6873

Specifications are subject to change without notice. No liability or warranty implied by this information. Environmental compliance based on producer documentation.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Mountain Switch:](#)

[107-3021-EVX](#)