





MATERIAL:  
BODY & COVER - 16 GA. [1.5mm] C.R.S.  
INTERNAL PANEL - 14 GA. [2.0mm] C.R.S.  
WALL MTG. BRKTS - 14 GA. [2.0mm] TYPE 430 STAINLESS STEEL  
STRIKER - C.R.S.  
HINGE PINS & WALL MTG. HARDWARE - TYPE 201 STAINLESS STEEL  
LATCH - ZINC DIE CAST  
GASKET - 0.38 [9.5] THK. ROGERS CORP. PORDON #4701-30-15375-04 (BLACK)  
SEALING WASHERS - BLACK NEOPRENE  
HOLE PLUGS - LIGHT GRAY NEOPRENE

FINISH:  
BODY & COVER - LIGHT GRAY SMOOTH POWDER COAT  
INTERNAL PANEL - ZINC PLATED  
WALL MOUNTING BRACKETS & HINGE PINS - NATURAL  
STRIKER - ZINC PLATED  
LATCH - CHROME PLATED



BOXES SUPPLIED WITH GROUNDING KIT THAT CONTAINS THE FOLLOWING: (1) GROUND WIRE, (4) FLAT WASHERS, (2) SPLIT LOCKWASHERS AND (2) HEX NUTS

| PART NO. | "A"        | "B"        | "C"        | "D"          | "E"           | "F"        | "G"          | "H"          | "J"        | "K"        | "L"        | "M"        |
|----------|------------|------------|------------|--------------|---------------|------------|--------------|--------------|------------|------------|------------|------------|
| SNB-3730 | 9.84 [250] | 7.87 [200] | 5.91 [150] | 5.33 [135.4] | 11.12 [282.3] | 6.42 [163] | 8.25 [209.6] | 6.28 [159.6] | 6.89 [175] | 4.92 [125] | 8.46 [215] | 5.91 [150] |
| SNB-3738 | 7.87 [200] | 5.91 [150] | 5.91 [150] | 5.33 [135.4] | 9.15 [232.3]  | 4.45 [113] | 6.28 [159.6] | 4.31 [109.6] | 4.92 [125] | 2.95 [75]  | 6.50 [165] | 3.94 [100] |
| SNB-3739 | 7.87 [200] | 7.87 [200] | 3.98 [101] | 3.40 [86.4]  | 9.15 [232.3]  | 6.42 [163] | 6.28 [159.6] | 6.28 [159.6] | 4.92 [125] | 4.92 [125] | 6.50 [165] | 5.91 [150] |
| SNB-3740 | 9.84 [250] | 9.84 [250] | 5.91 [150] | 5.33 [135.4] | 11.12 [282.3] | 8.39 [213] | 8.25 [209.6] | 8.25 [209.6] | 6.89 [175] | 6.89 [175] | 8.46 [215] | 7.87 [200] |
| SNB-3741 | 9.84 [250] | 7.87 [200] | 3.98 [101] | 3.40 [86.4]  | 11.12 [282.3] | 6.42 [163] | 8.25 [209.6] | 6.28 [159.6] | 6.89 [175] | 4.92 [125] | 8.46 [215] | 5.91 [150] |