




API TK36
DIN Rail

8 and 11 Pin Sockets, Standard and Finger-Safe, Surface or DIN-Rail Mountable

ELECTRICAL RATING

API 008 600 Volts, 10 Amps
API 008 FS, API 011, API 011 FS 300 Volts, 10 Amps

CONSTRUCTION

Contacts Brass, Nickel Plated
Screws Binder Head, 6-32 x 1/4" Steel Zinc Plated
Pressure Clamp, 6-32 x 5/16" Steel, Zinc Plated
Wire Range #12 to #22 AWG Solid or Stranded
Screws, FS Box Lug, M3 Steel, Nickel Plated
Maximum Wire Gauge #14 AWG
Molding Black Break-Resistant Thermoplastic

AGENCY APPROVALS

Standard Models UL recognized File No. E60008
FS models UL recognized File No. E113714
Standard Models CSA certified File No. LR29513
FS models CSA certified File No. LR26716
All Models CE

SOCKETS



API 008 8 Pin Octal
API 008 FS 8 Pin Octal, Finger Safe
API 011 11 Pin Octal Style
API 011 FS 11 Pin Octal Style, Finger Safe

ACCESSORIES DESCRIPTION



API TK36 Prepunched Aluminum DIN Rail (1 Meter Lengths)



API Sockets API 008 and API 008 FS



API 011 and API 011 FS Sockets





Model	Description
API 008	8-pin socket, DIN rail or surface mount
API 008-5A	8-pin socket, DIN rail or surface mount, with 5 A current shunt, 0.1 Ω 25W 1% shunt resistor
API 008 FS	8-pin socket, finger-safe, DIN rail or surface mount
API 011	11-pin socket, DIN rail or surface mount
API 011-5A	11-pin socket, DIN or surface mount, with 5 A current shunt, 0.1 Ω 25W 1% shunt resistor
API 011 FS	11-pin socket, finger-safe, DIN rail or surface mount
API TK36	Aluminum DIN rail, 39" long
API CLP1	Hold-down spring for API 008, API 008 FS, API 011 or API 011 FS
API GP8	Green 8-pin plug for 55 mm DIN housing. Each



API CLP1
Hold-down spring for API 008, API 008 FS, API 011 or API 011 FS sockets



API 008-5A
Socket with current shunt




API GP8 Green plug for 55 mm DIN housing




API TK36 Aluminum DIN Rail, 39" Long


API 008-05A Socket with Shunt




API 008-5A
8-Pin Socket/Shunt
600 V Rating



API 011-05A Socket with Shunt



API 011-05A
11-Pin
Socket/Shunt
300 V Rating



API maintains a constant effort to upgrade and improve its products. Specifications are subject to change without notice. Consult factory for your specific requirements.