




| SIZE | STYLE  | A±.015<br>[0.38] | B±.005<br>[0.13] | C±.005<br>[0.13] | D±.005<br>[0.13] | E BSC.           |
|------|--------|------------------|------------------|------------------|------------------|------------------|
| E09  | PIN    | 1.213<br>[30.81] | -----            | .666[16.92]      | .984<br>[24.99]  | .432<br>[10.97]  |
|      | SOCKET |                  | .643[16.33]      | -----            |                  |                  |
| A15  | PIN    | 1.541<br>[39.14] | -----            | .994[25.25]      | 1.312<br>[33.32] | .756<br>[19.20]  |
|      | SOCKET |                  | .971[24.66]      | -----            |                  |                  |
| B25  | PIN    | 2.088<br>[53.04] | -----            | 1.534[38.96]     | 1.852<br>[47.04] | 1.304<br>[33.12] |
|      | SOCKET |                  | 1.511[38.38]     | -----            |                  |                  |
| C37  | PIN    | 2.729<br>[69.32] | -----            | 2.182[55.42]     | 2.500<br>[63.50] | 1.956<br>[49.68] |
|      | SOCKET |                  | 2.159[54.84]     | -----            |                  |                  |

|          |                               |                    |                                                                                                            |        |              |
|----------|-------------------------------|--------------------|------------------------------------------------------------------------------------------------------------|--------|--------------|
| MATERIAL | DRAWN I.ESSAJEE               | DATE 08/03/11      | Amphenol Canada Corp.                                                                                      |        |              |
|          | DESIGNED                      |                    |                                                                                                            |        |              |
|          | CHECKED K.LAMBIE              | 99/09/23           |                                                                                                            |        |              |
|          | I. E. APPRD.                  |                    |                                                                                                            |        |              |
| FINISH   | Q. A. APPRD.                  |                    | TITLE FCC17 FILTERED D-SUB, RIGHT ANGLE .405" [10.29] F/P, PIN & SOCKET - PLASTIC MTG. BRACKET & BOARDLOCK |        |              |
|          | DWG. APPRD.                   |                    |                                                                                                            |        |              |
|          | ENG. REL. NO.                 |                    |                                                                                                            |        |              |
|          | REF. EAR C1085B               |                    |                                                                                                            |        |              |
|          | DIMENSIONS ARE IN INCHES [mm] | CODE ID. NO. 03554 | DWG. DRAWING NO. P-FCC17-XXXXB-XX0X                                                                        | REV. A | SHEET 7 OF 7 |
|          | SCALE N.T.S.                  | WT. -----          | SURF. -----                                                                                                |        |              |