




FEATURES:

- Meets requirements of MIL-P-55149/1A.

MATERIALS:

Binding Post Body, Nuts, Lockwasher: Gold Plated Brass

Insulation: Nylon MIL-P-20693

Flat Washer: Brass

Insulator: Nylon

Hex Nut: Steel

RATINGS:

Voltage: Hand-held testing: 30VAC/60VDC Max.

Hands free testing in controlled voltage environments: 1500 VRMS

Operating Temperature: +80°C (+176°F) Max.

Current: 30 Amperes

ORDERING INFORMATION: Model 5018-*

*=Color, -0 Black, -2 Red, -4 Yellow, -5 Green, -6 Blue, -9 White

Ordering Example: 5018-2 Color is Red

All dimensions are in inches. Tolerances (except noted): .xx = ±.02" (.51 mm), .xxx = ±.005" (.127 mm).

All specifications are to the latest revisions. Specifications are subject to change without notice.

Registered trademarks are the property of their respective companies. Made in USA

All dimensions are in inches. Tolerances (except noted): .xx = $\pm .02$ " (.51 mm), .xxx = $\pm .005$ " (.127 mm).
All specifications are to the latest revisions. Specifications are subject to change without notice.
Registered trademarks are the property of their respective companies. Made in USA