



| PART NUMBER | "L" ±.010 (±0.25) | "A" REF. |
|---------------|----------------------|-------------|
| LEDS2M-120-01 | .12 (3.1) | .08 (2.0) |
| LEDS2M-140-01 | .14 (3.6) | |
| LEDS2M-160-01 | .16 (4.1) | |
| LEDS2M-180-01 | .18 (4.5) | |
| LEDS2M-200-01 | .20 (5.1) | |
| LEDS2M-220-01 | .22 (5.6) | |
| LEDS2M-240-01 | .24 (6.1) | .20 (5.1) |
| LEDS2M-250-01 | .25 (6.4) | |
| LEDS2M-260-01 | .26 (6.6) | |
| LEDS2M-280-01 | .28 (7.1) | |
| LEDS2M-300-01 | .30 (7.8) | |
| LEDS2M-320-01 | .32 (8.1) | |
| LEDS2M-340-01 | .34 (8.6) | .33 (8.4) |
| LEDS2M-360-01 | .36 (9.1) | |
| LEDS2M-380-01 | .38 (9.7) | |
| LEDS2M-400-01 | .40 (10.2) | |
| LEDS2M-420-01 | .42 (10.7) | |
| LEDS2M-440-01 | .44 (11.2) | |
| LEDS2M-450-01 | .45 (11.4) | .45 (11.4) |
| LEDS2M-460-01 | .46 (11.7) | |
| LEDS2M-500-01 | .50 (12.7) | .58 (14.7) |
| LEDS2M-550-01 | .55 (14.0) | |
| LEDS2M-600-01 | .60 (15.2) | .70 (17.8) |
| LEDS2M-650-01 | .65 (16.5) | |
| LEDS2M-750-01 | .75 (19.1) | |
| LEDS2M-850-01 | .85 (21.6) | |
| LEDS2M-900-01 | .90 (22.9) | |

NOTES:

1. MATERIAL: NYLON 6/6 UL 94 V-2 (RMS-01).
COLOR: NATURAL,
BLACK AVAILABLE BY SPECIAL ORDER.
2. FOR T-1 3/4 LED'S.

| | | | | | |
|-----|-----------------------------------|-------------|-------------------|-------------------------------|------------|
| H | SEE CO 200651 FOR CHANGES | SK 04.04.11 | TITLE: LED SPACER | DWG IN IN (MM) | FINAL |
| G | SEE CO 200649 FOR CHANGES | SK 04.01.11 | | | |
| F | SEE ECN #1168 FOR CHANGES | SK 05.19.06 | FILE # LEDS2M | DWN: D.D. | APP: |
| E | SEE ECN #892 FOR CHANGES | SM 12.14.04 | | | |
| D | SEE ECN #547 FOR CHANGES | SM 12.20.02 | MAT'L: SEE NOTES | DT: 05-20-96 | DT: |
| C | SEE ECN #526 FOR CHANGES | SM 11.21.02 | RE: RICHCO, INC. | RICHCO INC. | |
| B | CHANGED DIM "A" (SEE ENGINEERING) | SM 11.01.01 | | PO BOX 804238, CHICAGO, 60680 | |
| A | CHANGED FILE NO. AND TITLE BLOCK | SM 10.03.01 | FRAC=±1/64 | | SEE TABLE |
| REV | DESCRIPTION | ENGR DATE | ANG=±1' | | PRINT TYPE |
| | | | | | CA |