



Search Results

- Evaluate
- FAQ's
- How to Buy
- Bill of Material
 - Favorite Products List
 - Locate Distributor

Home > Product On-Line Catalog > Search Results >

Current refinements (click to remove) Search Tips [?](#)

Text Search: 'FSPX4855F165A'

Your search criteria matched only one product, shown below

FSPX4855F165A



- Connectivity meets or exceeds TIA/EIA-568-B.3 and ISO/IEC 11801 performance requirements
- Jacketed cable is compliant with NFPA 262 (OFNP) flame rating
- MTP* (12-fiber) connectors are FOCIS-5 compliant
- Insertion loss per mated pair: 0.50dB typical, 0.75dB max.
- PANDUIT proprietary MTP* polishing provides low insertion loss and high return loss, minimizing variability for improved channel link loss performance
- Factory terminated and 100% tested for insertion loss (test data supplied with each assembly); singlemode and 10Gig™ Multimode Trunk Cable Assemblies are also tested for return loss
- TIA/EIA-568-B.1-7 (Method A) standards based polarity supports 10 Gb/s, multimode, and singlemode fiber types, and allows infrastructure backwards compatibility for component interchangeability and a lower cost of ownership
- 10Gig™ laser optimized fiber is tested per IEEE 802.3ae 10 GbE to support network transmission speeds up to 10 Gb/s for link lengths up to 300 meters for OM3 and up to 550 meters for OM4

▪ Application specific designs available to tailor configuration, reach, and breakout construction to application requirements; for more information contact PANDUIT or visit www.panduit.com

*MTP is a registered trademark of US Conec Ltd

Standard lengths for MTP* to MTP* OM3/OM4, 12, 24 and 48 fiber are available from 40 to 200 feet in increments of 5 feet. Ex: FSPX1255F040A (40ft. length) to FSPX1255F100A (100ft. length.) Additional lengths are available. Please contact Customer Service for actual lead times.

Low Smoke Zero Halogen (LSZH) trunk cable assemblies available in EMEA only.

▪ Part Number	FSPX4855F165A
▪ RoHS Compliancy Status	Compliant
▪ Part Description	Female MTP* to female MTP* 48-fiber 10Gig™ 50/125µm OM3 multimode plenum rated trunk cable assembly with pulling eye on one end.
▪ Product Type	Trunk Cable Assemblies
▪ Length (ft.)	165
▪ Fiber Compatibility	10 GbE 50/125µm
▪ Fiber Cable Type	Round
▪ Fiber Type	Multimode
▪ Connector 1 Type	Female MTP*
▪ Connector 2 Type	Female MTP*
▪ End Configurations	Female MTP* to Female MTP*
▪ Fiber Count	48
▪ Flammability Rating	Plenum rated (OFNP)
▪ Pricing Description	48 Fiber Plenum OM3 Female MTP-Female MTP with pulling eye - 165 feet
▪ Min. Order UOM	PC
▪ Min. Order Qty.	1
▪ BOM Qty. (# of Pkgs.)	<input type="text" value="0"/>
▪ Add to Favorite Product List	<input type="checkbox"/>

Please [register](#) to utilize the 'Bill of Materials', 'Submit Quotes' and 'Favorite Product List' features.