


Binding Posts

164-R134B-EX, 164-R134R-EX

KOBICONN

Binding Posts



Dimensions: mm (in.)

MOUNT HOLE

SPECIFICATIONS

Rating:	10A / 125VAC
Contact Resistance:	50mΩ Max.
Insulation Resistance:	500V DC 100MΩ Min.
Dielectric Strength:	1000V AC 1 Minute
Tolerance:	±0.3 Except where noted
RoHS Compliant by Exemption	

Date Last Revised: 3/6/07

Available from Mouser Electronics
1-800-346-6873 / www.mouser.com

KC-301096

Specifications are subject to change without notice. No liability or warranty implied by this information. Environmental compliance based on producer documentation.

164-R134B-EX, 164-R134R-EX