

Part: 150274
 Series: 150 Series - In-Line Fuseholder for 2AG or 5x20mm Fuses
 Technology: Fuse Holders, Blocks and Clips - Electronic and Automotive Types

PARAMETERS		
Package Type	Pkg Type	Fuseholder
Mount Method	Mount	In-Line
Body Style for International Shock-Safe Fuseholders	Body	
Color of Device	Color	
For use with this UL Class or Fuse Type	Fuse Type	2AG
For use with this UL Class or Fuse Type	Fuse Type	5x20mm
Fuse Mounting Method	Fusemounting	Cartridge Fuses
Indicating	Indicating	N
Maximum Current Rating	Max (A)	10.0000
AC Voltage Rating	Max VAC (V)	32
Max DC Voltage	Max VDC (V)	32
Mounting Type	Mounting	In-Line
	special1	
	special2	
Terminal Style for International Shock-Safe Fuseholders	Terminal	"3/16"" NEMA QC"
For use with UL Class _____ Fuses	UL Class	Supplementary Protection

