








Copyright FCI.



PC card drilling dimensions(after plating)
(thickness 2.40±0.20mm)



Lead-free part-number

SHELL	A± 0.30	B± 0.12	C± 0.10	D± 0.25	E± 0.07	PART NUMBER
09	30.81	24.99	16.96	16.79	10.96	D09P24B.PA00LF
15	39.14	33.32	25.18	25.12	19.18	D15P24B.PA00LF
25	53.03	47.04	39.12	38.84	33.12	D25P24B.PA00LF
37	69.32	63.50	55.68	55.30	49.68	D37P24B.PA00LF

Standard part-number

SHELL	A± 0.30	B± 0.12	C± 0.10	D± 0.25	E± 0.07	PART NUMBER
09	30.81	24.99	16.96	16.79	10.96	D09P24B.PA00
15	39.14	33.32	25.18	25.12	19.18	D15P24B.PA00
25	53.03	47.04	39.12	38.84	33.12	D25P24B.PA00
37	69.32	63.50	55.68	55.30	49.68	D37P24B.PA00

Protection: 4 --> Flash AU

6 --> 0.76µ AU

GENERAL CHARACTERISTICS AND ROHS INFORMATIONS:
SEE DRAWING C01-8646-0000

European Views

rev	ecn no	dr	date
C	-	PJA	2004/10/21
D	LS05-001	MPE	2005/03/12
E	LS05-0056	MPE	2005/07/01
F	LS06-0097	LGO	2006/07/29
-	-	-	-
-	-	-	-
-	-	-	-

www.fciconnect.com			surface ISO 1302 ✓		tolerance std ISO 406 ISO 1101		projection 		mm 	
			TOLERANCES UNLESS OTHERWISE SPECIFIED							
Dr	LELEON	1992/09/14	ANGULAR	LINEAR	0.X	±0.1	size A3	Scale 2		
Eng	PESSON	1992/09/14			0.XX	±0.1				
Chr	LEGARE	1992/09/14			0.XX° ±2°	0.XXX		±0.1	ECN	LS06-0097
Appr	LEGARE	1992/09/14	Product family				D-SUB	Spec ref -		
			title MALE CRS DELTA D STD EUROPE STRAIGHT SOLDER TYPE FOR PCB 2.4mm				dwg no C01-8646-0102		Rev F	
catalog no			-				CUSTOMER		sheet 1 of 1	

REV F - 2006-04-17