

THA-203
THA-190

Flush Handle Latch Lift Lever



Characteristic

The handle can be used for both left and right side.

Application

Distribution boards /
Distribution panels /
Control boards

Specification

The key is exclusively used for THA-203.


Model No.	Type	Net Weight(g)	Code No.
THA-203-1	With Key	164.4	3965
THA-203-2		178.8	3966
THA-203-3		204.8	3967
THA-203-4		327.6	3968
THA-190-1	Without Key	156.4	3944
THA-190-1A		169.6	3940
THA-190-2		197.6	3945
THA-190-3		317.6	3946

Size of Holes for Installation and Plate Thickness

Model No.	a	b	c	d	Plate Thickness
THA-203-1・THA-190-1	72	63	24	φ 8	t0.5~t2.3
THA-203-2・THA-190-1A	85	76			
THA-203-3・THA-190-2	105	96			
THA-203-4・THA-190-3	128	117	27	φ 9	t1.0~t2.3


Parts List

No.	Part Name	Material	Finish	Quantity
1	Handle	ZDC	Silver Metallic	1
2	Body			1
3	Latch			1
4	Cam	SPCC	Zn	1
5	Set Screw for Cam	SWRM		2
6	Pan Shaped Washer	SPCC		2
7	Set Screw	SWRM		2
8	Key	ZDC	Cr(Satin Finish)	1




For THA-190

For THA-203



Layout of Holes for Installation



Shape of cam for THA-203-4-THA-190-3

Size List

Part No.	A	B	C	D	E	F	G	H	J	K	L	N	P	P1	Q	Q1	S	S1	S2	T	U	V	W	Y
THA-203-1-THA-190-1	84	32	28	19	72	62	2.5	14.5	t2~t2.3	φ 7	4	M4	40	35	70	30	35	10	20	M4	19	20	23	17
THA-203-2-THA-190-1A	97	44			85	75															25.5	31		
THA-203-3-THA-190-2	117	65			105	95															35.5	47		
THA-203-4-THA-190-3	141	86	32	21	128	116	3.0	17.0	t3.2	φ 8	5	M5	41.5	36	75	28.5	44	15	22	M5	45	65	26	19