



© COPYRIGHT 1976 BY AMP INCORPORATED, HARRISBURG, PA.
ALL INTERNATIONAL RIGHTS RESERVED. AMP INCORPORATED PRODUCTS
COVERED BY U. S. AND FOREIGN PATENTS AND/OR PATENTS PENDING.

REVISIONS					
P	F	ZONE	LTR	DESCRIPTION	DATE
			H	REV; EC OUIIC-0040-01	3-19-01
					DD
					EB



1. THE CONTACT SURFACES OF THE TERMINALS ARE COATED WITH LUBRICANT.
 2. ALL DIMENSIONS SHOWN ARE FOR REFERENCE ONLY UNLESS OTHERWISE SPECIFIED.
 3. MATERIAL: HOUSING, COVER AND CABLE CLAMP - THERMOPLASTIC
TERMINALS - GOLD OVER NICKEL PLATED
HIGH STRENGTH COPPER ALLOY.
HARDWARE - ZINC PLATED STEEL.
 4. COVER AND HARDWARE SHIPPED UNASSEMBLED.
 5. WIRE SIZE: 26-27-28 AWG 7 STRANDS OF COPPER CONDUCTORS. MAXIMUM INSULATION DIAMETER OF .045 IS ACCEPTABLE FOR MOST APPLICATIONS.
 6. KIT SHIPPED IN POLY BAG FORM.
- △ CORING MAY OR MAY NOT APPEAR AND IS AT THE DISCRETION OF AMP INCORPORATED.



.350-.425 DIA		BLACK	552403-1
CABLE RANGE		COLOR	PART NO
UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN INCHES. TOLERANCES ON: DECIMALS ± # ANGLES ± #		CONTRACT NO DR S. HEGE 5/27/76 CHK T. PIZZULO 5/27/76 APPD G. FOSTER 5/27/76 APPD [Signature] 1-5-90 OSGN APPD OTHER APPD	
MATERIAL △		NAME KIT, RECEPTACLE, 50 POSITION, E SLOT, CABLE TO CABLE, SCREW LOCK CHAMP-LOK®	
FINISH △		SIZE CODE IDENT NO DRAWING NO C 00779 552403	
SCALE 2/1		SHEET 1 OF 1	