




LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
H	—		G	REVISE PER ECO-10-018803	14SEP2010	LC	CW
			H	ECO-12-003005	22FEB12	SY	MQW
			J	ECR-12-009867	25NOV12	SY	AC





- NOTES:
- 1 MATERIAL CONTACT; PHOSPHORBRONZE
MATERIAL HOUSING; GLASSFILLED POLYESTER (GRAY)
UL-RATING 94V0.
 - 2 GENERAL PLATING SPECIFICATION: UNDERPLATING (ENTIRE CONTACT):
1,27µm NICKEL MIN. AND ACTION PIN: 0,5µm TIN-LEAD MIN.
FOR PLATING OF MATING SURFACES SEE APPLICABLE SPECIFICATION
REFERENCE FOR EACH DASH NUMBER.
 - 3 CONFORMS TO ALL TESTING ACCORDING IEC 61076-4-101
PERFORMANCE LEVEL 2.
 - 4 CONNECTOR PRINTED WITH PARTNUMBER AND DATECODE
 - 5 PLATED-THROUGH HOLES AT 2x2mm SQUARE GRID. 110 HOLES
 - 6 FITS WITH INTEGRATED GROUND RETURN UPPERSHIELD
BASIC P.N. 352151
 - 7 CONNECTOR TESTED AND QUALIFIED AGAINST TELCORDIA
GR-1217-CORE QUALITY LEVEL III, CENTRAL OFFICE APPLICATIONS.
 - 8 0.76µm MIN GOLD PLATING AT MATING SURFACES.



COMPONENT SIDE AS SHOWN
RECOMMENDED PCB-HOLE LAY-OUT

P.C.B. HOLE DIM. ACTION PIN
FOR DETAILS SEE
APPLICATION SPECIFICATION



	238	1	3-188836-0
OBSOLETE	2	1	188836-9
OBSOLETE	2	1	188836-1
	FINISH	MATERIAL	PARTNUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN E.MÖHLMANN CHK W.V.D.HEIJDEN APVD F.V.KONINGSBRUGGE PRODUCT SPEC 108-19082 APPLICATION SPEC 114-19029 WEIGHT —	11FEB97 — — — — — — —	Tyco Electronics Corporation s-HertogenBosch, Netherlands,	
DIMENSIONS: MM		TOLERANCES UNLESS OTHERWISE SPECIFIED:		NAME Z-PACK 2MM HM 110 POS. FEMALE DAUGHTER CARD CONN. (22 COLUMNS)	
MATERIAL —		FINISH —		SIZE A2	RESTRICTED TO —
CUSTOMER DRAWING		SCALE NTS		SHEET 1 OF 1	REV J