

PART NAME		NON-METALLIC ENCLOSURE (STYLE E)										PART No.		NBE-10543 AND NBE-10563									
MATERIAL:		SOLID BODY & COVER _____ ABS/PC BLENDED PLASTIC UL94-5VB FLAMMABILITY RATING CLEAR COVER _____ POLYCARBONATE PLASTIC UL94V-0 FLAMMABILITY RATING UV STABILIZED PANEL _____ 0.078 THICK ALUMINUM LATCHES & HINGES _____ NON-METALLIC WALL MOUNTING BRACKETS _____ STAINLESS STEEL										FINISH: BODY _____ LIGHT GRAY COVER _____ LIGHT GRAY OR CLEAR PANEL _____ ANODIZED COVER INCLUDES GRAY POLY-URETHANE GASKET.											
														INDUSTRY STANDARDS: UL508 TYPE 1, 2, 4, 4X INDOOR, 12 & 13 NEMA TYPE 1, 2, 4, 4X, 12 & 13 IEC529-IP65 AIR AND MOISTURE VENTS, GALVANIZED STEEL INTERNAL PANEL AND STAINLESS STEEL LOCKING HASP ARE NOT INCLUDED, BUT CAN BE PURCHASED SEPARATELY. UNIT COMES COMPLETE WITH (4) WALL MOUNTING BRKTS. & (4) M5 x 10mm LG. TRUSS HD. MACHINE SCREWS (NOT SHOWN)									
VIEW LESS COVER		VIEW LESS COVER AND SWINGFRAME PANEL												DIMENSIONS = INCHES [MILLIMETERS]									
NOTE: ALL DIMENSIONS HAVE ±0.039 [±1] TOLERANCE UNLESS OTHERWISE SPECIFIED																							
PART NO.		DIMENSIONS																					
SOLID COVER	CLEAR COVER	A	B	C	D	E	F	G	H	J	K	L	M	N	P	R	S	T	U	V	W	X	Y
NBE-10543	NBE-10563	7.475 [190]	6.650 [169]	6.150 [156]	5.900 [150]	4.717 [120]	2.960 [75]	11.280 [287]	10.462 [266]	9.955 [253]	8.860 [225]	8.278 [210]	6.902 [175]	4.330 [110]	1.185 [30]	10.600 [269]	10.640 [270]	6.800 [173]	6.840 [175]	6.227 [158]	5.460 [139]	10.335 [263]	9.220 [234]