


Dimensions: mm (In.)

**Electrical Specifications:**

- Contact resistance: 20mΩ (max)
- Dielectric Strength: 1000VAC for 1 min
- Insulation resistance: 100MΩ (min)
- Rating: 6A/125VAC, 3A/250VAC

Material:

- Internal Contact: Silver and Copper

() = Momentary contact

Mouser Stock No.	Type	Circuit
10TA320	SPST	On-Off
10TA330	SPDT	On-Off
10TA335	SPDT	On-Off-On
10TA345	SPDT	(On)-Off-(On)
10TA360	DPDT	On-On
10TA375	DPDT	(On)-Off-(On)

Miniature Toggle Switches
 10TA320, 10TA330, 10TA335, 10TA345,
 10TA360, 10TA375

**Mountain
Switch**

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Mountain Switch:

[10TA335](#) [10TA360](#) [10TA365](#) [10TA320](#) [10TA330](#) [10TA345](#)