


Technical datasheet: KPCM-G60H15C33-44DB-1176

Specifications:

Standard operation voltage	2VDC
Max operating voltage	10VDC
Output impedance	2.2kΩ
Frequency	100 Hz to 10,000 Hz
Sensitivity	-44dB±3dB
Sensitivity reduction	-3dB
Max. Current Consumption	0.5mA
Signal to noise ration	60dB
Directivity	Omni-directional

Dimensions:



Frequency Response:

