





JKL LAMP NUMBER	VOLTS RATED	AMPS ±10%	MSCP ±25%	LUMENS ±25%	AVERAGE LIFE HRS.	FILAMENT TYPE
SM0620M	6.0	.020	.024	0.30	5,000	C-6
SM0650M	6.0	.050	.080	1.01	5,000	C-2R
SM1220M	12.0	.020	.032	0.40	5,000	C-2V
SM1240M	12.0	.040	.088	1.11	5,000	C-2V
SM1250M	12.0	.050	.159	2.00	5,000	C-2V
SM2420M	24.0	.020	.064	0.80	5,000	C-2F
SM2430M	24.0	.030	.159	2.00	5,000	C-2F
SM2450M	24.0	.050	.279	3.51	5,000	C-2F
SM3020M	30.0	.040	.287	3.61	5,000	C-2F
SM3040M	30.0	.040	.287	3.61	5,000	C-2F

			METRIC  THIRD ANGLE PROJECTION		DIMENSIONS ARE IN MILLIMETERS TOLERANCE UNLESS OTHERWISE SPECIFIED 1 PL +/- 0.2 2 PL +/- 0 ANGLE +/- 0		JKL COMPONENTS CORPORATION			
			DRAWN BY		APPV'D BY		DATE		TITLE T-1 1/4 TELEPHONE SLIDE BASE LILIPUT T4.6	
			L. WENGSTROM		QC		8/16/00		SIZE A	
							FSCM NO.		DRAWING NO.	
							55335		SLIDE BASE LILIPUT T4.6	
RELEASED			8/16/00							
REV. NO.	DESCRIPTION/ECO NUMBER		APPV'D DATE		- CAD DRAWING - MANUAL REVISIONS NOT PERMITTED		SCALE		RELEASED DATE	
							NONE		8/16/00 REVISION DATE	
									REV. NO.	
									SHEET 1 OF 1	