


Stamped crimp contacts



Identification		Wire gauge (mm ²)	Part No.		
D-Sub	Performance levels Explanations see page 05.04 Other performance levels on request		stamped male contacts		
			Performance level 3	Performance level 2	Performance level 1
	Individual contacts	AWG 28-24 0.09-0.25 stranded	09 67 000 7177 ¹⁾	09 67 000 7178 ¹⁾	09 67 000 7176 ¹⁾
	500 pieces/reel Unrolling left		09 67 000 7167	09 67 000 7168	09 67 000 7166
	10 000 pieces/reel Unrolling left Unrolling left reversed Unrolling right reversed		09 67 000 7157 09 67 000 7147 09 67 000 7137	09 67 000 7158 09 67 000 7148 09 67 000 7138	09 67 000 7156 09 67 000 7146 09 67 000 7136
	Individual contacts	AWG 24-20 0.25-0.56 stranded	09 67 000 8177 ¹⁾	09 67 000 8178 ¹⁾	09 67 000 8176 ¹⁾
	500 pieces/reel Unrolling left		09 67 000 8167	09 67 000 8168	09 67 000 8166
	10 000 pieces/reel Unrolling left Unrolling left reversed Unrolling right reversed		09 67 000 8157 09 67 000 8147 09 67 000 8137	09 67 000 8158 09 67 000 8148 09 67 000 8138	09 67 000 8156 09 67 000 8146 09 67 000 8136
	Unrolling direction				
			for HARTING tools		

¹⁾ Minimum order 500 pieces or multiples of 500
Insertion and removal tool see chapter 20
Contact dimensions see page 05.29