

**151-00810**

Acrylic Adh. Bases, .18" Max tie width, 1.12" Length/Width, .18" Hole Dia., PA66UV, Black, 100/pkg

Article Number: 151-00810

Part Number: 151-00810

Type: MB4A

**Base Data**

Part No.	151-00810
Type	MB4A
Color	Black (BK)
Features	• For use with 18 and 50 pound cable ties to provide stability when securing bundles. • The UV stabilized mounts and VHB acrylic adhesive resists UV light and seals against moisture and environmental conditions, while providing strong bond to the surface. • 4 way opening allows cable ties to be installed parallel or perpendicular to wire bundles.
Application Method	These mounting bases can be secured to a surface using rubber based adhesive, acrylic adhesive, or also can be screw mounted.
Typical Application	The UV stabilized mounts and VHB acrylic adhesive resists UV light and seals against moisture and environmental conditions, while providing strong bond to the surface.

Product Dimensions

Length (L)	1.12" / 28.5mm
Width (W) (imperial)	1.12"
Width (W)	28.5mm
Max. Cable Tie Width	0.18" / 4.6mm
Height (H)	0.23" / 5.8mm
Mounting Hole Ø	0.18" / 4.6mm

Mounting Hole Centers 0.80" / 20.2mm

Material and Specifications

Material Polyamide 6.6 UV-stabilized (PA66UV)

Flammability UL94 V2 (excluding adhesive)

Material Specification RoHS

Operating Temperature -40 °F to +185 °F (-40 °C to +85 °C)

ROHS Conformity  RoHS

UL Listed (US and Canada) No

UL Recognized (US and Canada) Yes

Logistic and Packaging

Packaging Type bag

Pkg. Qty. 100

EAN code 4031026408217

© HellermannTyton North America 2011 | [TS16949](#), [ISO 9001](#) and [ISO 14001 Certified](#)
7930 N. Faulkner Rd. Milwaukee, WI 53224-9517 | Fax: 800-848-9866 | Phone: 800-537-1512