




NOTES:

1. HARDWARE SUPPLIED.
2. DIELECTRIC WITHSTAND VOLTAGE: 1500VAC
3. MAX. MOUNTING TORQUE: 8lbs-in.

CAPACITANCE	10nF±20%
TEMP. RANGE	-55°C/+125°C
CURRENT	25 AMPS
WORKING VOLTAGE @125°C	600 VDC 240 VAC MAX., 400Hz
DC RESISTANCE	.001 OHMS MAX.
IL=PER MIL-STD-220	
FREQ. MHz	I.L. (db)
1	3
10	20
100	35
1 GHz	57
10GHz	57
SCHEMATIC	
MARKING:	PART:SCI 54-844-002
BUBBLE	PACK:SCI 54-844-002
DATE CODE	LOT NO.
QTY./PACK (25 PCS.)	



	16	15	14	13	12	REV. NO.	TOLERANCES UNLESS OTHERWISE SPECIFIED	api  FAIRVIEW PENNSYLVANIA technologies corp.	
	CN 69683-ENG	CN 212779	CN 202139	CN 187805	CN 184928	CHANGE NOTICE	Fractions ± 1/64		
							Dec. .xx±	Dwn. SLAGLE	Description
							Dec. .xxx± .010	Date 7-29-13	LOW PASS EMI FILTER
							Angles ±0° 30'	Engr. B. DEVINE	
							CODE IDENT. NO. DLSP2	Scale NONE	54-844-002