


THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

PANDUIT PART NO.*	RECOMMENDED FASTENER	'A'	'B'	'C'	'D'	'E'	'F'	'G' 'REF'	'H' 'REF'	'I' 'REF'	USE WITH THESE CABLE TIE CROSS SECTIONS	WEIGHT (g) lbs/100 pcs.
TM3S8	#8 (M4) SCREW	0.863 [21.9]	0.610 [15.5]	0.373 [9.4]	0.320 [8.1] ±.020 [0.5]	0.088 [2.2] ±.020 [0.5]	0.208 [5.3]	0.105 [2.7]	0.325	0.180	MINIATURE INTERMEDIATE STANDARD LT. HEAVY	0.369 [167.5]
TM3S10	#10 (M5) SCREW							0.115 [2.9]	0.385	0.200		0.363 [165.0]
TM3S25	1/4" (M6) SCREW	0.879 [22.3]	0.629 [16.0]	0.379 [9.6]			0.210 [5.3]	0.155 [3.9]	0.506	0.262		0.296 [134.5]
TM3S2510	#10 (M5) SCREW	0.873 [22.2]	0.620 [15.7]				0.212 [5.4]	0.120 [3.0]	0.480	0.200		0.321 [145.5]


NOTES:

*1. SEE www.panduit.com FOR CURRENT PART NUMBER SUFFIX DESIGNATION AND FOR PACKAGE SIZE AND PART COLOR.
SEE www.panduit.com FOR TEFZEL, METAL DETECTABLE AND PEEK MOUNT DRAWINGS.


2. HOLE DIMENSIONS SHOULD ACCOMMODATE SPECIFIED RECOMMENDED FASTENER.



SEE NOTE 2



SECTION A - A



DIMENSIONS IN BRACKETS ARE METRIC [mm]

TITLE				TM3S - TIE MOUNT			
CUSTOMER DRAWING							
ITEM REVISION NAME				108015KD/00			
DATASET FILE NAME				108015KD_DC/00 - GB0239EN_REV12			
UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: IN [mm]				PANDUIT MATERIAL: SEE NOTE 1			
.X ± .1 [2.54] .XXX ± .005 [0.127] .XX ± .01 [0.25] ANGLES ± 5°							
THIRD ANGLE PROJECTION				DRAWING NUMBER: GB0239EN			
DRAWN BY	DATE	CHK	SCALE	SHT 1 OF 1		SIZE	
AJV	12/17/96		NONE			A	

12	6/27/13	BWG	JADE	RTF I	REVISED CHART AND NOTE 1. SEE ECN FOR FULL DETAILS.	GB0239EN/12
REV	DATE	BY	CHK	APR	DESCRIPTION	ECN