



FEATURES:

- Mates to Standard Double Banana Jacks
- Extends to 48, 60 or 72 respectively.

MATERIALS:

Conn: 1st end – Double Banana Plug.

Material: Spring; One piece heat treated Beryllium Copper, Berylco 25 per QQ-C-533.

Plug body; Brass per QQ-B-626, alloy 360, 1/2 Hard.

Finish: Nickel plated per QQ-N-290, class 2, 200/300 microinches.

Insulation: Polypropylene molded to plug bodies and cable. Color: Black.

Marking: "3864 POMONA ELECTRONICS CO. INC. POMONA CALIFORNIA".

Wire: Retractile cord; 24 AWG, stranding 45x40 tinned copper, rubber insulation, 4.32 (.170) O.D.

Color: Black.

Conn: 2nd end – Same as first end.

RATINGS: (Entire Assembly)

Operating Temperature.: +50°C. (+122°F.) Max.

Operating Voltage: 270 VDC/90 VAC

ORDERING INFORMATION: Model 3864-XX

XX=Wire, Standard Lengths: 48" (1219), 60" (1524), 72" (1829)

Ordering Example: 3864-72 is 72" (1829) length fully extended

All dimensions are in inches. Tolerances (except noted): .xx = ±.02" (.51 mm), .xxx = ± .005" (.127 mm).

All specifications are to the latest revisions. Specifications are subject to change without notice.

Registered trademarks are the property of their respective companies. Made in USA

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Pomona:

3864-48 3864-72