





NOTES:

- 1 MAXIMUM RECOMMENDED STROKE .500
- 2 FOR USE WITH THE 206-375 TOOL. FOR OTHER TOOLS AND/OR STROKE COMBINATIONS, REFER TO THE STROKE LIMITER CHART (HK1122) OR CONSULT AN AFS/HUCK SPECIALIST.
- 3 SHIP WITH: STOP 126747, DEFLECTOR 126748-1 AND (2) .030 SHIMS 128290 REFERENCE PB563 FOR PROPER USE.
- 4 128624C ASSEMBLY CONSISTS OF 128514C COLLET AND 128488 DRAWBAR.
- 5 128336-08C ASSEMBLY CONSISTS OF 127078C ANVIL HOLDER AND 127207-08 ANVIL INSERT



REV	DESCRIPTION	DET	DATE
D	REWROTE NOTES; ADDED .453 CENTER TO EDGE DIMENSION		11/24/09
E	128514C WAS 128624C. ADDED 128488	JJC	08/03/12

E	128488	1	DRAWBAR	9
	126748-1	1	UNITIZED DEFLECTOR	8
E	128514C	1	COLLET	7
	126745	1	GUARD	6
	120095	1	DEFLECTOR	5
	122912	1	BARBED RETAINER	4
	128075	1	UNITIZED CHUCK JAW	3
	127582	1	TOP GUARD	2
	128336-08C	1	ANVIL ASSEMBLY	1
	PART NO.	QTY	DESCRIPTION	ITEM

IDENTIFICATION PER SPEC 42-311: ★ ETCH			
ITAR:	HUCK INTERNATIONAL, INC., I.S.D. 1 CORPORATE DR, P.O. BOX 2270 KINGSTON, NEW YORK 12401		
ECCN: EAR99	NOSE ASSEMBLY -08 UAB BR LONG		
SCH B#: 8467.99.0190	DET: MJK	CK:	DATE: 11/15/06 SCALE: 2:1
HTS: 8467.99.0190	B	99-3766-1C	