



GST 140 BCE Professional Jigsaw

The new standard in precision

- High-precision saw blade guidance due to double roller reduces saw blade bending – for excellent cut precision
- Tool-free, secure-fitting saw blade changing system (SDS) prevents the saw blade from wobbling to ensure maximum surface quality
- Compact, lightweight design with small grip circumference enables optimum control when sawing
- Very low vibration due to mass balance system for top-class running smoothness
- High-performance LED ensures particularly bright illumination of the cutting area
- Powerful 720-watt motor with Constant Electronic offers power reserves for deep cuts even in the hardest materials
- Systematic precision: compatible with new guide rail and our “Extra-Clean for Wood” saw blades for tear-free cuts
- Compatible with all Bosch extractors for clean work
- Robust magnesium base plate with tool-free adjustment

Technical data: GST 140 BCE Professional

Rated power input	720 W
No-load stroke rate	800 – 2.800 spm
Weight	2,3 kg
Saw, stroke length	26 mm

Cutting depth

Cutting depth in wood	140 mm
Cutting depth in aluminium	20 mm

Rated power input 720 W

Cutting depth in non-alloyed steel 10 mm

Functions

- Pendulum stroke adjustment
- Bosch SDS System
- Electronic
- Constant Electronic

Noise/vibration information

Measured values determined according to EN 60745
Total vibration values (vector sum of three directions)

Sawing wood

Vibration emission value ah 7.0 m/s²

Uncertainty K 1.5 m/s²

The A-rated noise level of the power tool is typically as follows: Sound pressure level 82 dB(A); Sound power level 93 dB(A). Uncertainty K= 3 dB

Complete with: GST 140 BCE Professional

1 saw blade T 244 D
ET no. 2 609 991 423 ✓

1 saw blade T 308 B
ET no. 2 609 991 830 ✓

2 saw blades T 144 DP
ET no. 2 609 991 424 ✓

Anti-splinter guard
2 601 016 096 ✓

Dust extraction set
ET no. 2 605 510 301 ✓

L-BOXX inlay
2 608 438 042 ✓

L-BOXX
2 608 438 692 ✓