


OGA DIAGONAL: 18.25 [463.63]
VA DIAGONAL: 17.54 [445.50]
PA DIAGONAL: 16.54 [420.12]

TOP LEVEL NUMBER	US NUMBER	TYPE	DIM "A" (TOTAL GLASS TO CONNECTOR)	A/G FINISH	PROD SPEC
17-8421-203	98-0003-2589-8	FFC	4.27" [108.46]	AG500	23655
17-8421-221	98-0003-2596-3	SER	4.27" [108.46]	AG500	23655
17-8421-204	98-0003-2590-6	FFC	6.00" [152.40]	AG500	23655
17-8421-223	98-0003-2597-1	SER	6.00" [152.40]	AG500	23655
17-8421-227	98-0003-2599-7	SER	8.00" [203.20]	AG500	23655
17-8421-205	98-0003-2591-4	FFC	8.00" [203.20]	AG500	23655
17-8421-206	98-0003-2190-5	NOV	SEE DWG	AG500	23655
17-8421-218	98-0003-2594-8	USB R	4.27" [108.46]	AG500	23655
17-8421-220	98-0003-3151-6	USB R	6.00" [152.40]	AG500	23655
17-8421-226	98-0003-3152-4	USB R	8.00" [203.20]	AG500	23655
17-8421-230	98-0003-2276-2	HID M	8.00" [203.20]	AG500	23655
N/A	98-0003-3537-6	HID D	8.00" [203.20]	AG500	23655
N/A	98-0003-3974-1	DUAL	8.00" [203.20]	AG500	23655
N/A	98-1100-0095-1	FFC	8.00" [203.20]	WC100	34523
N/A	98-1100-0096-9	USB R	8.00" [203.20]	WC100	34523



NOTES:

1. WEIGHT OF GLASS IN GRAMS: 804±10%
2. NICOMATIC HOUSING P/N: OLO5
3. NICOMATIC RECEPTACLES (PINS) MATTE TIN PLATED P/N: 14106-12
4. HOUSING ORIENTED WITH LATCH DOWN

PINOUT	
1	LL
2	UL
3	SHLD
4	UR
5	LR

UNITS INCHES [MM]

TOLERANCES UNLESS OTHERWISE SPECIFIED
.X ± .03 [.76]
.XXX ± .015 [.38]
ANGLES ±1°

THIRD ANGLE PROJECTION

DO NOT SCALE DRAWING

SCALE 1 = 1



3M TOUCH SYSTEMS
METHUEN, MA
USA

© COPYRIGHT 2004
THIS DOCUMENT IS COPYRIGHTED PROPERTY OF THE
3M COMPANY AND MAY NOT BE REPRODUCED
WITHOUT 3M WRITTEN PERMISSION OR USED OR
DISCLOSED FOR OTHER THAN 3M AUTHORIZED
PURPOSES.

DRAWN K CROWLEY 08/05

CAD FORMAT AUTOCAD

SIZE C DOCUMENT NO. TSD-28165

P	REVISED PER CO 036265	4/13	SEB
N	REVISED PER CO 036100	2/13	SEB
REV	CHANGE NOTICE	DATE	DRW

TITLE	MARKETING DRAWING SCT32NN 17.54"
SHEET	1 OF 1
SIZE	C
DOCUMENT NO.	TSD-28165
REV	P